




REV	DESCRIPTION	DET	DATE
D	ITEM 3, 130053 WAS 123189	EL	11/10/11
E	128522C WAS 128632C. ADDED 128487	JJC	08/02/12



- NOTES:
- 1 MAXIMUM RECOMMENDED STROKE .500
 - 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
 - 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-3 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
 - 4 128632C ASSEMBLY CONSISTS OF 128522C COLLET AND 128487 DRAWBAR.



(E)	128487	1	DRAWBAR	9
	126748-3	1	UNITIZED DEFLECTOR	8
(E)	128522C	1	COLLET	7
	126745	1	GUARD	6
	120095	1	DEFLECTOR	5
	122727-1	1	BARBED RETAINER	4
	130053	1	UNITIZED CHUCK JAW	3
	127582	1	TOP GUARD	2
	127095C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH		HUCK INTERNATIONAL, INC., I.S.D 1 CORPORATE DR KINGSTON, NEW YORK 12401	
ITAR/ECCN: EAR99		CLEARANCE NOSE ASSEMBLY -05 MLGP STRADDLE	
SCH B#: 8467.99.0190		FINAL ASSY: -	
HTS: 8467.99.0190	ENG: MVM CK:	DATE: 10/20/04	SCALE: 2:1
	B 99-3744C		