



LUMISPOT LED LIGHT ENGINES SINGLE COLOR



Patents pending


OPERATING CONDITIONS

- ▲ Recommended PCB temp=55°C
Maximum PCB temp = 105°C
- ▲ LED Life @ 55°C PCB temp = 50,000 hours
- ▲ For maximum performance efficiency and longevity, all "LumiSpot" LED Light Engines should be screwed or affixed using thermal adhesive to an appropriate heat sink
- ▲ Maximum current = 350mA
- ▲ Thermal conductivity = 1.3W/m-k
- ▲ Breakdown voltage = 2kV

MECHANICAL DIMENSIONS

Height (all models including lens) = 15.5mm (0.61")
 Spot1, Diameter = 21.5mm (0.85")
 Spot3, Diameter = 48.0mm (1.89")
 Spot6, Diameter = 69mm (2.72")
 (inside diameter = 23mm) (0.91")
 Spot9, Diameter = 90mm (3.54")
 Lead wire length 12" (on equipped models)

PART NUMBERS



of LEDs (A)

1 = 1 LED / Spot 1
 3 = 3 LEDs / Spot 3
 6 = 6 LEDs / Spot 6
 9 = 9 LEDs / Spot 9

LED Color (B)

W = Cool White
 WW = Warm White
 R = Red
 G = Green
 B = Blue
 A = Amber

LENS Type (CCC)**

005 = 5 Degree
 015 = 15 Degree
 025 = 25 Degree
 520 = 5 X 20 Degree
 XXX = no lens*

* This figure indicates half-divergence angle

** Lens to be purchased and installed separately

FEATURES / BENEFITS

- ▲ Extremely long life of 50,000 hours at 55°C PCB temperature
- ▲ Durable F-Form optics holder allow for easy changing of 4 lens options (5, 15, 25 degree + 5x20 degree oval)*
- ▲ Available in 6 colors (cool white, warm white, red, blue, green, amber)
- ▲ Aluminium based PCB for easier heat dissipation and more efficient operation
- ▲ Units with production dates of 8/07 or later come with 22 AWG 12" lead wires pre-attached (red+ / black-)

APPLICATIONS

Any application requiring efficiency & long life in a circular, flood, spot or oval light pattern.

MATERIALS/FINISH

- ▲ LUXEON® I LEDS
- ▲ 1.6mm Aluminium clad PCB substrate
- ▲ White solder resist finish


Dialight reserves the right to make changes at any time in order to supply the best product possible.

1501 Route 34 South • Farmingdale, NJ 07727 USA
 Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com




MDEXLUMSPOT_D

PHOTOMETRIC DATA



ELECTRICAL SPECIFICATIONS



TYPICAL LED PHOTOMETRIC DATA

LED	Color	Forward Voltage (Typ)	Max. Current (mA)	Max. Power (Watts)	Dom Wavelength / CCT			Min Luminous Flux (lm) / Radiometric Power (mW)	Typ Luminous Flux (lm) / Radiometric Power (mW)
					Min	Typ	Max		
	Red	2.95	350	1.03	620.5 nm	627 nm	645 nm	30.6 lm	44 lm
	Green	3.42	350	1.20	520 nm	530 nm	550 nm	30.6 lm	53 lm
	Royal Blue	3.42	350	1.20	440 nm	455 nm	460 nm	145 mW	220 mW
	White	3.42	350	1.20	4500 K	5500 K	10000 K	30.6 lm	45 lm
	Amber	2.95	350	1.03	584.5 nm	590 nm	597 nm	23.5 lm	42 lm
	W White	3.42	350	1.20	2850 K	3300 K	3800 K	13.9 lm	20 lm

Results are LED manufacturer's test data @ 25°C JTC'. Light output at 55°C PCB temperature will be approximately 15-20% lower. Elevated temperatures will result in further degradation of light output. For maximum performance use appropriate heat sinking.

Maximum current input 350mA
Maximum power consumption
1.2W per LED for White / Blue / Green / Warm White, 1.0W per LED for Red / Amber.
Recommended min gauge wire, AWG24

Dialight reserves the right to make changes at any time in order to supply the best product possible.

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com



MDEXLUMSPOT_D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[LSP-9W025](#) [LSP-9W005](#) [LSP-9W015](#) [LSP-6W520](#) [LSP-9BXXX](#) [LSP-6B025](#) [LSP-6B005](#) [LSP-6B015](#) [LSP-6WWXXX](#) [LSP-9WW015](#) [LSP-3W520](#) [LSP-9WW005](#) [LSP-9WW025](#) [LSP-1G520](#) [LSP-6WXXX](#) [LSP-3WWXXX](#) [LSP-3WW520](#) [LSP-9G015](#) [LSP-9B520](#) [LSP-6G520](#) [LSP-9G025](#) [LSP-9G005](#) [LSP-6WW520](#) [LSP-6R520](#) [LSP-9R015](#) [LSP-9R005](#) [LSP-9R025](#) [LSP-9W520](#) [LSP-3BXXX](#) [LSP-1G015](#) [LSP-9GXXX](#) [LSP-1G005](#) [LSP-1G025](#) [LSP-9RXXX](#) [LSP-3W015](#) [LSP-3W005](#) [LSP-3W025](#) [LSP-3WW015](#) [LSP-3WW005](#) [LSP-3WW025](#) [LSP-1WXXX](#) [LSP-6R015](#) [LSP-6R005](#) [LSP-6R025](#) [LSP-9B025](#) [LSP-6G025](#) [LSP-6WW015](#) [LSP-6G005](#) [LSP-9B005](#) [LSP-9B015](#) [LSP-6B520](#) [LSP-6G015](#) [LSP-6WW025](#) [LSP-6WW005](#) [LSP-3RXXX](#) [LSP-3GXXX](#) [LSP-9WXXX](#) [LSP-9WW520](#) [LSP-3R015](#) [LSP-3R005](#) [LSP-6BXXX](#) [LSP-3R025](#) [LSP-3G025](#) [LSP-1B005](#) [LSP-1B025](#) [LSP-3G005](#) [LSP-3G015](#) [LSP-1B015](#) [LSP-9R520](#) [LSP-6W015](#) [LSP-9G520](#) [LSP-6W005](#) [LSP-9WWXXX](#) [LSP-6W025](#) [LSP-6RXXX](#) [LSP-1B520](#) [LSP-3G520](#) [LSP-3R520](#) [LSP-6GXXX](#) [LSP-3WXXX](#) [LSP-1WWXXX](#)