



# No-Clean Desoldering Braid

1814-1825

Desoldering braid (wick) is pre-fluxed copper braid that is used to remove solder, which allows components to be replaced and excess solder to be removed.  
 Techspray wick is available in static dissipative bobbins (except where indicated) for static sensitive environments.



**No-clean flux coated braid -- cleanest in the industry!**  
 Techspray NoClean wick does not leave behind ionic flux residues that can collect and form branches called "dendrites". Other fluxes, if not cleaned properly, can cause dendrites that grow over time (see A, B) and eventually cause short circuits between traces or leads (C). Latent failures lead to costly returns and lower the quality perception of your products.

Size chart:

Braid #  
 Color Code  
 Width (in)  
 Width (mm)

#1  
 White  
 0.035  
 0.9

#2  
 Yellow  
 0.055  
 1.4

#3  
 Green  
 0.075  
 1.9

#4  
 Blue  
 0.098  
 2.5

#5  
 Brown  
 0.130  
 3.3

#6  
 Red  
 0.193  
 4.9



- No-clean flux coated braid
- Cleanest wick -- clear, non-reactive residues
- Will not leave ionic residue -- avoid dendrite failure
- Exceeds MIL-F-14256, Type
- Anti-static spool (except where indicated)

Product Packaging

1814-100F  
No-Clean White #1 Braid  
100'  
1 units/case



1815-5F  
No-Clean Yellow #2 Braid  
5'  
25 units/case



1815-10F  
No-Clean Yellow #2 Braid  
10'  
25 units/case



1815-100F  
No-Clean Yellow #2 Braid  
100'  
1 units/case



1815-500F  
No-Clean Yellow #2 Braid  
500'  
1 units/case



1816-5F  
No-Clean Green #3 Braid  
5'  
25 units/case



1816-10F  
No-Clean Green #3 Braid  
10'  
25 units/case



1816-50F  
No-Clean Green #3 Braid  
50'  
1 units/case



1816-100F  
No-Clean Green #3 Braid  
100'  
1 units/case





1816-500F  
No-Clean Green #3 Braid  
500'  
1 units/case



1817-5F  
No-Clean Blue #4 Braid  
5'  
25 units/case



1817-10F  
No-Clean Blue #4 Braid  
10'  
25 units/case



1817-100F  
No-Clean Blue #4 Braid  
100'  
1 units/case



1817-500F  
No-Clean Blue #4 Braid  
500'  
1 units/case



1820-5F  
No-Clean White #1 Braid - AS  
5'  
25 units/case



1820-10F  
No-Clean White #1 Braid - AS  
10'  
25 units/case



1820-50F  
No-Clean White #1 Braid - AS  
50'  
1 units/case



1821-5F  
No-Clean Yellow #2 Braid - AS  
5'  
25 units/case



# TECHSPRAY®

## Technical Data Sheet



1821-10F  
No-Clean Yellow #2 Braid - AS  
10'  
25 units/case



1821-25F  
No-Clean Yellow #2 Braid - AS  
25'  
1 units/case



1821-50F  
No-Clean Yellow #2 Braid - AS  
50'  
1 units/case



1822-5F  
No-Clean Green #3 Braid - AS  
5'  
25 units/case



1822-10F  
No-Clean Green #3 Braid - AS  
10'  
25 units/case



1822-50F  
No-Clean Green #3 Braid - AS  
50'  
1 units/case



1822-100F  
No-Clean Green #3 Braid - AS  
100'  
1 units/case



1823-5F  
No-Clean Blue #4 Braid - AS  
5'  
25 units/case



1823-10F  
No-Clean Blue #4 Braid - AS  
10'  
25 units/case





1823-25F  
No-Clean Blue #4 Braid - AS  
25'  
1 units/case



1823-100F  
No-Clean Blue #4 Braid - AS  
100'  
1 units/case



1824-5F  
No-Clean Brown #5 Braid - AS  
5'  
25 units/case



1823-25F  
No-Clean Blue #4 Braid - AS  
25'  
1 units/case



1825-5F  
No-Clean Red #6 Braid - AS  
5'  
25 units/case



1824-25F  
No-Clean Brown #5 Braid - AS  
25'  
1 units/case



1824-25F  
No-Clean Brown #5 Braid - AS  
25'  
1 units/case



1825-5F  
No-Clean Red #6 Braid - AS  
5'  
25 units/case

**Chemical & Physical Properties**

|               |  |
|---------------|--|
| Appearance    |  |
| Odor          |  |
| Flash Point   |  |
| VOC (EPA)     |  |
| VOC (CARB)    |  |
| Boiling Point |  |
| Density       |  |

**Chemical Composition**

| CHEMICAL NAME                                            | CAS #     |
|----------------------------------------------------------|-----------|
| Non-ionic flux mixture (Proprietary non-hazardous blend) | 7440-50-8 |





Copper

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

North America

Techspray  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
email: [tsales@techspray.com](mailto:tsales@techspray.com)

Europe

ITW Contamination Control BV  
Saffierlaan 5  
2132 VZ Hoofddorp  
The Netherlands  
+31 88 1307 400  
email: [info@itw-cc.com](mailto:info@itw-cc.com)

Countries Outside US

Call to locate a distributor in your country

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.