





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

- NOTES: 1. FOR USE WITH PANDUIT MSW50T15-CR4 & MSW50T15-CR6 CONTINUOUS STRAPPING. ^(A)
2. APPLICATION TOOL: BT2MS75, BT2HT
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS
4. UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:
.XX = $\pm .02$ [.5]
.XXX = $\pm .010$ [.25]
5. MATERIAL: 304 OR 316 STAINLESS STEEL



							TITLE .500 in [12.70] ENHANCED METAL STRAPPING BUCKLE Ⓟ MSBW50-C4 & MSBW50-C6 CUSTOMER DRAWING					
03A 3/13 JAMB MIM RGR0 UPDATED DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO SSECN01042							ITEM REVISION NAME N41148BS/03			PANDUIT		
02A 10/08 JAMB SKB --- ORIG CAD FILE SPEC WAS S41148_02. NOTE 2: APPLICATION TOOL BT1HT REPLACED BY BT2HT -----							DATASET FILE NAME N41148BS_DC/03A					
02 10/04 JAMB EJD JJB ⓅSTRAPPING PART NO'S. IN TITLE BLOCK CHANGED TO BUCKLE PART NO'S., DUE TO TYPING ERROR 12067							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .005 [.127] .XX ± .01 [.25] ANGLES ± 5 ° THIRD ANGLE PROJECTION					
01 9/04 JAMB EJD JJB ⓂVOIDED PART NO'S. MSW50T15-TSR & MSW50T15-TSR316 & REPLACED BY PART NO'S. MSW50T15-CR4 & MSW50T15-CR6 ON NOTE 1 12052												
00 9/03 BRH EJD JJB DRAWING RELEASED 11154							DRAWING NUMBER: N41148BS_DC					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY BRH	DATE 9/03	CHK EJD	SCALE 2:1	SHT 1 OF 1	SIZE A