


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301230064](#)
Status: **Active**
Overview: [Aero-Motive Wire-Rope Festoon Systems](#)
Description: I-Beam Festoon Intermediate Car 638 S4, for 4.0" I-Beam, Urethane Wheels



Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Festoons
Series	130123
Cable Height - Maximum	25.40mm (1.000")
Cable Width - Maximum	151.38mm (5.960")
Combined Cable Weight-Max./Car	79.38kg (175.0 lb)
Component Type	Car - Intermediate
Depth	209.55mm (8.250")
Duty	Heavy
Height	336.55mm (13.250")
Length	325.88mm (12.830")
Overview	Aero-Motive Wire-Rope Festoon Systems
Product Name	Aero-Motive
Type	I-Beam
UPC	78678863079

Physical	
Beam Size	S4 - 101.60mm
Material - Coating	Powder Coating
Material - Metal	Steel
Material - Wheel	Polyurethane
Net Weight	2.980/kg
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	112.78mm (4.440")
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Flat

Material Info	
Engineering Number	0638410

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130123](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION