



General ordering data

Order No.	0637320000
Part designation	SAKG 32/35 II
Version	Special terminal, special connections, 50 mm ² , Screw connection, KrG, Medium yellow, TS 35
EAN	4008190018276
Qty.	10 pc(s).

Product notes

Note, technical data	Conductor connection with cable lugs according to DIN 46234 and DIN 46235, from 10 .. 70 mm ²
----------------------	---

Additional technical data

Colour of insulating material	Medium yellow
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 35
Insulating material	KrG
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	Open
Operating temperature range	- 60 °C, + 130 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	5VA
Version	Stud terminal

CSA rating data

Voltage (CSA)	600 V
CSA current	170 A
Min. cross-section (CSA)	AWG 1
Max. cross-section (CSA)	AWG 2/0

Conductors for clamping (rated connection)

Clamping range, min.	10 mm ²
Clamping range, max.	70 mm ²
Type of connection	Screw connection

Conductors for clamping (rated connection)

2nd type of connection	screwed
Connection direction	on side
No. of connections	1
Clamping screw	M 8
Tightening torque range	6.0...12 Nm
AWG conductor size, min.	AWG 6
AWG conductor size, max.	AWG 3/0
AWG conductor size, min.	26.67 mm ²
AWG conductor size, max.	67.44 mm ²

Dimensions

Width	32 mm
Height of lowest version	53 mm
Length	80 mm
TS 32 offset	22.5 mm
TS 35 offset	40 mm

Rating data

Rated cross-section	50 mm ²
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Rated current	150 A
Standards	IEC 60947-7-1
Current with max. conductor	192 A
Pollution severity	3

UL rating data

Voltage (UL)	600 V
Current (UL)	200 A
Min. cross-section (UL)	AWG 6
Max. cross-section (UL)	AWG 3/0

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000897
ETIM 3.0	EC000897
eClass 4.1	27-14-11-31
eClass 5.0	27-14-11-31
eClass 5.1	27-14-11-31

Similar products

Order No.	Part designation	Version
0637120000	SAKG 32/35 I	Special terminal, special connections, 50 mm ² , Screw connection, KrG, Medium yellow, TS 35
0637420000	SAKG 32/35 II/GW	Special terminal, special connections, 50 mm ² , Screw connection, KrG, Medium yellow, TS 35
0637220000	SAKG 32/35 III	Special terminal, special connections, 50 mm ² , Screw connection, KrG, Medium yellow, TS 35