




Wiha 3K Series Screwdrivers and Sets

3K Ergonomic Series Screwdrivers & Sets

Blades made of
CVM tool steel,
chromed shaft

Hole in handle
for hanging



Dual material handle has
molded soft grip panels

Exact fit precision
machined black tips



450 Slotted Screwdriver, With Wiha-3K Series Handle

Blade chrome-vanadium-molybdenum steel, chrome nickel-plated.
Wiha-3K Ergo handle, cushion grip. Precision black tips.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
450 40**	2.5	.10	75	3.0	0.4	.02	161	6.3	.06	10
450 50**	3.0	.12	100	3.9	0.5	.02	185	7.3	.07	10
450 52**	3.5	.14	100	3.9	0.6	.02	197	7.7	.09	10
450 54**	4.0	.16	100	3.9	0.8	.03	206	8.1	.12	10
450 55	4.5	.18	100	3.9	1.0	.04	207	8.1	.13	10
450 56	4.5	.18	150	5.9	1.0	.04	257	10.1	.14	10
450 57	4.5	.18	200	8.0	1.0	.04	306	12.0	.15	10
450 58	5.5	.22	125	5.0	1.0	.04	243	9.5	.19	10
450 60	6.0	.24	100	3.9	0.9	.04	218	8.5	.20	10
450 61	6.0	.24	150	5.9	0.9	.04	268	10.5	.23	10
450 62	6.0	.24	200	8.0	0.9	.04	318	12.5	.25	10
450 64*	6.5	.24	40	1.6	1.2	.05	90	3.5	.08	10
450 65	6.5	.24	150	5.9	1.2	.05	268	10.5	.23	10
450 67	8.0	.35	150	5.9	1.2	.05	268	10.5	.26	10
450 69	10.0	.39	200	8.0	1.6	.06	318	12.5	.35	10

* Stubby screwdriver with Wiha Powerhandle - 45064

** Cabinet Tip



484 01 1/4" Bit holding Screwdriver, With Wiha-Ergo 3K Handle

Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM tool steel, nickel plated.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
484 01	1/4"	125	5.0	211	8.3	.24	1



451 Phillips Screwdriver, With Wiha-3K Series Handle

Item No.	mm	Inch	mm	Inch	lbs.	pkg.
451 35	0		60	2.4	5.7	.06 10
451 37	1		80	3.1	7.3	.13 10
451 40	1		200	8.0	12.0	.16 10
451 42	2		100	3.9	8.5	.21 10
451 44	2		150	5.9	10.5	.23 10
451 47	2		200	8.0	12.5	.25 10
451 50*	2		40	1.6	90	3.5 .08 10
451 52	3		150	5.9	268	10.5 .31 10

* Stubby screwdriver with Wiha Powerhandle - 45150



460 98 Set 4 Pcs. Slotted & Phillips

Item No.	mm	mm	Size	mm	lbs.
460 98	450 55	4.5	100	451 37	1 80
	450 60	6.0	100	451 42	2 100



460 99 Set 40 Pcs. Slotted, Phillips, TORX®, Pozidriv®, Bit Holder & Folding Ruler Blade CVM steel, hardened. With 16" tool box

Item No.	lbs.
460 99	10.4

● **Slotted:** 2.5, 3.0, 3.5, 4.0, 4.5x100, 4.5x150, 4.5x200, 5.5, 6.0x100, 6.0x150, 6.0x200, 6.5x40, 6.5x150, 8.0, 10mm
 ⊕ **Phillips:** 0x60, 1x80, 1x200, 2x100, 2x150, 2x200, 2x40, 3x150
 ⚙ **TORX®:** T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T45, T50
 ⊕ **Pozidriv®:** 1x80, 2x100
 3K 1/4" Magnetic Bit Holder
 61601 Folding Ruler