



Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	4 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1-1/8 in.
Stud Size	N/A
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	GRAY
Panduit Die Index No. on Barrel	P29
Alternate Industry Die Index No. () on Barrel	(8)



Technical drawing of a Panduit LCC4-00W cable jacket. The drawing shows a side view of the cable with the following dimensions and markings:

- Overall Length:** 3.09 ± 0.06
- Outer Diameter:** .62 ± .04
- Markings:**
 - PANDUIT (with a circular logo)
 - 4 STR CU
 - LCC4-00W
 - Color coded barrel markings (indicated by a line pointing to the barrel)
 - DATE 01/10/01



						 PANDUIT CORP. TINLEY PARK, ILLINOIS	
						LCC4-00W-L	
01	4/04	DRL	DRL	REMOVED NAVY NUMBER	11746	Copper Lug - Blank Tongue, Long Barrel with Window	
REV	DATE	BY	CHK	DESCRIPTION	ECN	SCALE N/A	DRAWING NO / CAD FILE LCC4-00W-CUST