

Thermal Mini Printer
AP1300 and AP1310 Series



H=47, W=92, D=108mm



H=65, W=95, D=128mm

- Compact, portable and stylish
 - Single handed paper load operation
 - High speed and high quality fixed head thermal mechanism
 - Choice of serial RS232, IrDA or Bluetooth interface
 - Applications include mobile ticketing and recording, PDA printing, utility billing, in-vehicle receipting, test and measurement equipment and medical systems
 - AP1300 has 16m roll capacity and AP1310 has 38m roll capacity
 - Choice of rechargeable or primary cell battery power (Note: The AP1310-DP is a mains powered only version with UK, Euro and USA mains plugs and no batteries)
 - Linerless, label sticky paper roll is available
 - An optional fast charger is available which has both mains and 12V in-car inputs
- Contents: Printer, rechargeable battery pack, cradle for AA batteries, UK/US/euro mains trickle charger, 2 paper rolls, D9 data cable, wall mount bracket, belt clip and user guide
- | | | | |
|---------------------|--|---------------------|---------------------|
| Specification: | AP1300/AP1310 | AP1300-IR/AP1310-IR | AP1300-BT/AP1310-BT |
| Order Code | 109-5829/109-5832 | 109-5830/109-5834 | 109-5831/109-5835 |
| Data input | RS-232 | RS-232 | RS-232 |
| Wireless data input | N/A | IrDA | Bluetooth |
| Printer type | Fixed head thermal mechanism (Fujitsu FTP-628MCL103) | | |
| Print speed | 60 mm/s (at 7.2V battery voltage); 50 mm/s (typical) | | |
| Print Width | 48 mm | | |
| Dots per line | 384 | | |
| Dot spacing | 8 dots/mm (vertical and horizontal) | | |
| Weight | AP1300 series: 330g (including battery and paper roll)
AP1310 series: 446g (including battery and paper roll) | | |

419105

Mftrs. List No.	Order Code	Price Each
AP1300	109-5829●	
AP1300-IR	109-5830●	
AP1300-BT	109-5831●	
AP1310	109-5832●	
AP1310-IR	109-5834●	
AP1310-BT	109-5835●	
AP1310-DP	109-5836●	
Paper Roll, AP1300, 15m	109-5837	
Paper Roll, AP1310, 33m	109-5838	
Linerless Roll, 18x8.5m, AP1300	135-0610	
Linerless Roll, 8x28m, AP1310	135-0611	
Fast Charger (Mains/in-car)	109-5839●	