



REV.	DATE	DESCRIPTION
NC	09/24/06	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex								
7						DRAWN	G.R.S.	09/24/06										
6						CHECKED			PART DESCRIPTION SMA PANEL RECEPT. JACK —									
5						ISSUED												
4						SHEET	1 OF 1											
3	CONTACT PIN	BER. COPPER	GOLD	1	DO NOT SCALE DRAWING	CAD FILE		C:/132/132142.DWG		PART NO.		132142						
2	INSULATOR	TEFLON	NATURAL	1						DWG. NO.		132142.DWG	REV.	NC	SIZE	A	SCALE	NA
1	BODY	BRASS	GOLD	1														
	DESCRIPTION	MATERIAL	FINISH	QTY														