

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74526-1004](#)
Status: **Active**
Overview: [LaneLink™](#)
Description: 0.50mm Pitch LaneLink™ 10Gbase-CX4 Cable Assembly, 28 AWG, Lanyard Latch, 3.0m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Test Summary TS-74526-001 \(PDF\)](#)

Agency Certification

UL E72548

General

Product Family Cable Assemblies
Series [74526](#)
Connector to Connector 4X Plug-to-4X Plug
Overview [LaneLink™](#)
Product Name 10Gbase-CX4, LaneLink™
UPC 822348270590

Physical

Cable Length 3.0m
Circuits (Loaded) 4X
Gender Male-Male
Lock to Mating Part Yes
Net Weight 334.596/g
Packaging Type Bag
Single Ended No
Waterproof / Dustproof No
Wire Insulation Diameter N/A
Wire Size AWG 28
Wire/Cable Type Parallel Pair

Electrical

Current - Maximum per Contact 0.5A
Impedance 100#
Shielded Yes
Voltage - Maximum 30V AC

Material Info

Reference - Drawing Numbers

Sales Drawing SD-74526-100
Test Summary TS-74526-001



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74526Series](#)

Mates With
[91525](#) 4X/12X Latch LaneLink™
Receptacle. [91804](#) LaneLink™ Connector

Use With
[74735](#) X2 Transceiver. [74739](#) XPAK
Transceiver

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74526-1004