








REV	ECN	APP'D
-	5277	JT 12-28-05
A	6078	6/14/07



- NOTES:
1. MATERIALS-
 SOCKET BODY: POLYETHERIMIDE PER ASTM-D-5205
 GROMMET: SILICONE RUBBER PER A-A-59588
 CONTACT RETAINERS: STAINLESS STEEL
 THREADED INSERTS: STAINLESS STEEL
 MOUNTING HARDWARE: STAINLESS STEEL
 2. PART MEETS APPLICABLE REQUIREMENTS OF MIL-PRF-12883/44.
 3. PART ACCEPTS M39029/101-553 SOCKET CONTACTS, SIZE 20/20 (SEE TABLE).
 4. MOUNTING HARDWARE SEE TABLE.
 5. WEIGHT: .024 LBS (10.9 GRAMS), NOT INCLUDING HARDWARE AND CONTACTS.
 6. OPERATING TEMPERATURE: -65° C TO 125° C.

APCD P/N	HARDWARE SUPPLIED	CONTACT PKG SUPPLIED
JRE400100	NO	NO
JRE400101	NO	YES
JRE400110	YES	NO
JRE400111	YES	YES

SCALE 2:1
MOUNTING CONFIGURATION

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd SPECIFICATION DRAWING		TITLE RELAY SOCKET QUICK-MOUNT 4-POLE, 5-AMP				
ANSI Y14.5M UNITS: INCHES Pro/E FILE	.XX ±0.01 .XXX ±0.005 ANGLES ±2.0°		ENGR S. KONDO 17-Mar-04						
ORIGINAL 	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD PEABODY, MA, USA	CHKD  6/12/07	SIZE A	DWG NO. JRE400100			REV A		
		APPD JACK TON 12-28-05	CODE: 58982		SCALE: NONE	SHEET 1 OF 1			