

Adapter plate - HC-B 24-ADP-B 16-OG - 1774995

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Adapter plates, from type to type, for HEAVYCON wall cutouts, cutout 36 x 86 mm, for type B24 to B16



The illustration shows version HC-B 24-ADP-B 16, in orange



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 037963
Weight per Piece (excluding packing)	32.22 GRM
Custom tariff number	85472000
Country of origin	Germany

Technical data

Dimensions

Length	150 mm
Height	52 mm
Hole diameter	4.5 mm
Width	2 mm
Drill hole distance, horizontal	130 mm
Drill hole distance, vertical	32 mm
Internal cutout dimension	36 x 86 mm

General

Color	orange
Design	B24 to B16

Adapter plate - HC-B 24-ADP-B 16-OG - 1774995

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 3.0	EC002309
ETIM 4.0	EC002309
ETIM 5.0	EC002309

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--

Adapter plate - HC-B 24-ADP-B 16-OG - 1774995

Drawings

