

RHINO 5200

PROFESSIONAL LABELING TOOL

Show off your work with the RHINO™ 5200 from DYMO® — designed for professional installers who work in real-world jobsite conditions.



DYMO exclusive "hot keys" automatically size, space and format labels for wires and cables, terminal blocks, electrical and patch panels, 110-blocks, vertical and fixed-length applications.

Pre-programmed symbol library > 100 puts industry symbols, punctuation, currency and fractions at your fingertips.

Save more than 100 customized labels for on-demand printing at the job site.

Smart on-screen alerts help prevent mistakes and wasted labels.



Large two-line display – backlit for poorly-lit jobsites.

Automatic shut-off maximizes battery life.

Prints on Rhino industrial-strength labels from 6mm to 19mm wide.

Prints Code 39 and Code 128 bar codes on 19mm labels.

Slip-resistant, built-in rubber bumper protects printer against damage from accidental falls and rough conditions.

- Datacom
- Electrical
- Facility Maintenance
- Professional A/V
- Security

www.dymo.com/rhinoacademy

RHINO
DYMO®

LABELS THAT STICK & STAY STUCK

RHINO 5200 LABELS

Applications

120 Volts

1

Flat Surfaces

2

Curved Surfaces

3

Cable

Flexible nylon

12mm • 19mm

Part #

S0718100

S0718120

S0718080

S0718090

Description

White Flexible Nylon Tape 12mm

White Flexible Nylon Tape 19mm

Yellow Flexible Nylon Tape 12mm

Yellow Flexible Nylon Tape 19mm

Length

3,5m

3,5m

3,5m

3,5m

Permanent polyester

9mm • 12mm • 19mm

Part #

S0718240

S0718210

S0718220

S0718160

S0718170

S0718180

S0718200

Description

White Perm Polyester Tape 9mm

White Perm Polyester Tape 12mm

White Perm Polyester Tape 19mm

Clear Perm Polyester Tape 9mm

Metallized Perm Polyester Tape 9mm

Metallized Perm Polyester Tape 12mm

Metallized Perm Polyester Tape 19mm

Length

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

Vinyl

9mm • 12mm • 19mm

Part #

S0718580

S0718600

S0718620

S0718440

S0718450

S0718470

S0718480

S0718490

S0718500

S0718510

S0718520

S0718530

S0718550

S0718560

S0718570

Description

White Vinyl 9mm

White Vinyl 12mm

White Vinyl 19mm

Yellow Vinyl 9mm

Yellow Vinyl 12mm

Yellow Vinyl 19mm

Orange Vinyl 9mm

Orange Vinyl 12mm

Orange Vinyl 19mm

Red Vinyl 9mm

Red Vinyl 12mm

Red Vinyl 19mm

Green Vinyl 9mm

Green Vinyl 12mm

Green Vinyl 19mm

Length

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

Heat shrink tube

6mm • 9mm • 12mm • 19mm

Part #

S0718260

S0718280

S0718300

S0718330

S0718270

S0718290

S0718310

S0718340

Description

White Heat Shrink Tube 6mm

White Heat Shrink Tube 9mm

White Heat Shrink Tube 12mm

White Heat Shrink Tube 19mm

Yellow Heat Shrink Tube 6mm

Yellow Heat Shrink Tube 9mm

Yellow Heat Shrink Tube 12mm

Yellow Heat Shrink Tube 19mm

Cable Diameter

Min 1,18mm Max 2,33mm

Min 1,73mm Max 3,73mm

Min 2,97mm Max 5,13mm

Min 4,64mm Max 8,70mm

Min 1,18mm Max 2,33mm

Min 1,73mm Max 3,73mm

Min 2,97mm Max 5,13mm

Min 4,64mm Max 8,70mm

Length

1,5m

1,5m

1,5m

1,5m

1,5m

1,5m

1,5m

1,5m

Non-adhesive Tag

6mm • 9mm • 12mm • 19mm

Part #

S0718350

S0718360

S0718380

S0718390

S0718400

S0718410

S0718420

S0718430

Description

White Non-Adhesive Tag 6mm

White Non-Adhesive Tag 9mm

White Non-Adhesive Tag 12mm

White Non-Adhesive Tag 19mm

Yellow Non-Adhesive Tag 6mm

Yellow Non-Adhesive Tag 9mm

Yellow Non-Adhesive Tag 12mm

Yellow Non-Adhesive Tag 19mm

Length

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

5,5m

Label Colors

CL
Clear

Yellow

Red

Orange

Green

White

Metallized

RHINO labels are easy to use and super-strong.

Thanks to industrial-strength adhesives, they deliver the lasting durability and legibility you demand – for a multitude of applications. To meet your high standards, RHINO labels are designed to work exclusively with RHINO printers and perform on a variety of surfaces (smooth, curved, textured and highly textured).

- Industrial-strength adhesives help these labels stick and stay stuck – in harsh worksite conditions.
- Thermal transfer print technology produces labels that are durable, smear-proof and resistant to chemicals, solvents, heat, UV and more.

IDEAL LABEL APPLICATIONS

Flexible Nylon

wire, cable, curved & highly textured surfaces

Permanent Polyester

flat surfaces such as panels; textured and rough surfaces; can be used outdoors

Vinyl


flat or curved surfaces; can be used outdoors

Heat Shrink Tubes

wires & cables; slides on and won't fall off

Non-adhesive Tags

inserts or other applications where adhesive is not required



Easy-to-peel split backing

RHINO5200 SINGLE UNIT (BOXED)

S0841460

EAN: 3501170841464

Box includes:

Rhino5200 printer

User manual on CD-rom

Quick reference guide

19mm white flexible nylon tape

12mm white vinyl tape

Rechargeable lithium-ion battery pack

AC adapter

1 year warranty

Unit weight: 0,90 kg

Units per master carton: 4

Master carton dimensions (LxWxH): 30,00 cm x 19,40 cm x 34,50 cm

Master carton weight: 4 kg

RHINO5200 HARD CASE KIT

S0841390

EAN: 3501170841396

Hard case kit includes:

Rhino5200 printer

User manual on CD-rom

Quick reference guide

19mm white flexible nylon tape

12mm white vinyl tape

Rechargeable lithium-ion battery pack

AC adapter

1 year warranty

Unit weight: 2,50 kg

Units per master carton: 3

Master carton dimensions (LxWxH): 38,60 cm x 37,20 cm x 49,83 cm

Master carton weight: 7,80 kg

PRODUCT SPECIFICATIONS:

Runs on 6 AA batteries or optional lithium-ion rechargeable battery

PRODUCT SPECIFICATIONS:

Runs on included lithium-ion rechargeable battery with AC adaptor or optional 6 AA batteries

For more information or to find your nearest distributor, please visit www.dymo.com or call us at (+44) 020 7341 55 29.

DYMO

Produced by: DYMO bvba
Industriepark Noord 30
B-9100 Sint-Niklaas-Belgium

Newell Rubbermaid

A Newell Rubbermaid Company
www.sanfordbrands.com
Made in Belgium

RHINO
DYMO

S0901630