




BRIDGE RECTIFIERS, Surface Mount, Dual In Line

ISi Part Number	Maximum Average Rectified Current at T _a		Peak Inverse Voltage	Peak Forward Surge Current @ 8.3ms Superimposed	Max Forward Voltage @ Rated I _F and T _a =25°C	Max Reverse Current @ Rated PIV and T _a =25°C	Reverse Recovery Time @ Rated PIV	Pkg Quant	Outline
	I _F (Amps)	T _a (°C)	PIV (Volts)	I _{FSM} (Amps)	V _{FM} (Volts)	I _R (uA)	T _{RR} (nsec)	Tube/Reel	inches/millimeters
SDB101	1.0	40	50	50	1.1	10	N/A	50 1500	
SDB102			100						
SDB103			200						
SDB104			400						
SDB105			600						
SDB106			800						
SDB107			1000						
DF005S	1.0	40	50	50	1.1	10	N/A	50 1500	
DF01S			100						
DF02S			200						
DF04S			400						
DF06S			600						
DF08S			800						
DF10S			1000						
EDF-1AMS	1.0	40	50	50	1.05 Glass Passivated Ultra-Fast Recovery	5.0	50	50 1500	
EDF-1BMS			100						
EDF-1CMS			150						
EDF-1DMS			200						