



FEATURES:

- Provides a simple means of connection between equipment with both SMA and Type N jacks.
- SMA and N connectors feature PTFE dielectric and tarnish resistant shells for superb electrical performance.
- Gold center contacts assure noise free connections.

MATERIALS:

Type N Male: Body and Fittings – Brass, Tarnish Resistant

Center Contact – Brass, Gold Plated

Dielectric - PTFE

Coaxial Cable: RG142B/U, Double Shielded, O.D. .195" (4,95mm)

SMA Male: Body and Fitting – Steel, Finish – Passivated Steel

Center Contact – Brass, Gold Plated

Dielectric – PTFE

RATINGS:

Operating Temperature: +200°C (+329°F) Max.

Operating Voltage: 335 VRMS Max.

Connector/Cable Impedance: 50 Ohms

ORDERING INFORMATION: Model 5058-X-xx

xx = Cable Length in Inches, Standard Lengths: 36" (91.44cm), 48" (122cm), 60" (152.4cm)

Additional lengths can be quoted upon request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA