

Data Sheet

Programmable DC Power Supplies
Models 1785B, 1786B, 1787B & 1788

Programmable DC Power Supplies

Models 1785B, 1786B, 1787B & 1788 are Programmable DC Power Supplies that offer new levels of "ease of use" and programmable functionality. Direct key in entry makes voltage and current selection fast, accurate and easy. In case calibration allows for simple, cost savings, uninterrupted operation.

Common Features:

- Sixteen user programmable preset outputs
- Controllable Output On/Off Switch
- 10 mV/10 mA settable resolution
- Closed case calibration
- Low ripple and noise
- Excellent temperature stability
- Serial interface cable and software included



Model 1788

Specifications	1785B	1786B	1787B	1788
Parameter				
Output Ratings, (0 °C - 40 °C)				
Voltage	0 ~18 V	0 ~32 V	0 ~72 V	0 ~32 V
Current	0 ~5 A	0 ~3 A	0~1.5 A	0~6 A
Load Regulation, ±(% of output +offset)				
Voltage	<0.01% + 3 mV , Model 1788 = <0.02% + 5 mV			
Current	<0.1% + 3 mA			
Line Regulation, ±(% of output +offset)				
Voltage	<0.1% + 3 mV			
Current	<0.1% + 2 mA			
Ripple, (20 Hz ~20 MHz)				
Voltage	≤ 1 mVrms/3 mVpp			
Current	5 mArms			
Dimensions (WxHxD)	10" x 4.16" x 15" (255.7 mm x 105.7 mm x 382.7 mm)			
Weight	14 lbs (6.4 kg)	16.5 lbs (7.5 kg)		
One Year Warranty				
Included Accessories	User manual, software Installation disk, test report, power line cord, IT-E131 RS232 to TTL serial converter cable			