




TNC Connectors, 50 Ohm (Continued)

Jacks, Crimp

Dual Crimp

Weatherproof

Mil Type



Connector Cable Range Selection Code ¹	RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	M39012/ Military No. and/or Comments	Part No.	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 678304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1
B	174, 174A, 188, 188A, 316	Dual Crimp	Gold	Nickel	Polymethyl-pentene	Commercial		414171-3	1.200 30.48	—	318450-2	—
B3	RJ-88, 316 Double Braid	Dual Crimp	Gold	Nickel	Polymethyl-pentene	Commercial		414171-4	1.200 30.48	—	58539-1	—
D	58, 58A, 58B, 58C	Dual Crimp	Gold	Nickel	TEFLON	Mil Type	—	225400-2	1.375 34.93	220045-2	—	—
		Dual Crimp	Gold	Silver	TEFLON	Mil Type	2780005 Weatherproof	225551-2	1.406 35.72	220045-2	—	—
D, D1	58, 58A, 58B, 58C, 141, 141A, 303	Dual Crimp	Gold	Nickel	Polymethyl-pentene	Commercial		414171-1	1.175 29.65	—	220189-1	—
D1	141, 141A, 303	Dual Crimp	Gold	Silver	TEFLON	Mil Type	2780015 Weatherproof	225551-5	1.406 35.72	220045-2	—	—
E	55, 55A, 55B, 223	Dual Crimp	Gold	Silver	TEFLON	Mil Type	2780016	225551-1	1.406 35.72	220045-2	—	—
		Dual Crimp	Gold	Nickel	Polymethyl-pentene	Commercial	—	414171-6	1.175 29.65	—	220189-1	—
E ⁺	142, 142A, 142B, 400	Dual Crimp	Gold	Silver	TEFLON	Mil Type	2780006 Weatherproof	225551-6	1.406 35.72	220045-2	—	—
		Dual Crimp	Gold	Nickel	Polymethyl-pentene	Commercial	—	414171-5	1.350 34.29	—	220189-1	—
G	124, 140, 210, 62, 62A, 623, 69, 69A, 59B, Belden 9251, 9209, 9269	Dual Crimp	Gold	Nickel	TEFLON	Mil Type	—	225400-3	1.218 30.94	220045-3	—	—
		Dual Crimp	Gold	Nickel	Polymethyl-pentene	Commercial	—	414171-2	1.175 29.65	—	220189-2	—

¹Refer to pages 14 and 15 for code specifications.