



Ty-Rap®

T&B Catalog Number: TY253M
UPC Number: 78621083990
Description: Cable Tie 50lb 11" Natural Nylon with Stainless Steel Locking Device Bulk Pack

Status: Active

General

Material Nylon 6.6
Color Natural

Dimension Information

Length (inches) 11.6
Width (inches) .187
Max. Wire Bundle Diameter (inches) 3

Specifications

Military Standard Part No. MS3367-7
Tensile Strength (lbs.) 50
Temperature Rating -40°F to 185°F
Flamability Rating UL 94 V-2

Tooling

Application Tools ERG50, WT1-TB

Packaging

T&B Order Multiple 1000
T&B Inner Pack 1000
Package in Units 5000
Package Type Bulk
T&B Sold in UOM Each
T&B Weight Per UOM 0.43 lbs. per 100

Application Support

Overview Available on Website
Material Selection Guide Available on Website
Available Colors Available on Website

Certifications

RoHS Compliance Yes

Cable Ties

Ty-Rap® Nylon 6.6 Cable Ties



TY523M — Tie body width .091"



TY524M — Tie body width .140"



TY525M — Tie body width .187"



TY5272M — Tie body width .270"



STD. PKG. CAT. NO.	BULK PKG. CAT. NO.	BODY WIDTH IN./MM	LENGTH IN./MM	MAX. WIRE BUNDLE DIA. IN./MM	MILITARY STANDARD PART NO.	TENSILE STRENGTH LBS./N.	STD. PKG. QTY.	BULK PKG. QTY.
TY523M	TY23M	.09/2.29	3.62/91.95	.63/16.00	MS3957-4	18/80.07	100	1,000
TY52315M	TY2315M	.09/2.29	7.00/177.80	1.50/38.10	—	18/80.07	100	1,000
TY5232M	TY232M	.09/2.29	8.00/203.20	2.00/50.80	—	18/80.07	100	1,000
TY5234M	TY234M	.09/2.29	14.00/355.60	4.00/101.60	—	18/80.07	100	1,000
TY524M	TY24M	.14/3.56	5.50/139.70	1.13/28.70	MS3957-5	40/177.90	100	1,000
TY5242M	TY242M	.14/3.56	8.19/208.03	2.00/50.80	—	40/177.90	100	1,000
TY526M	TY26M	.14/3.56	11.10/281.94	3.00/76.20	—	30/133.40	100	1,000
TY5244M	TY244M	.14/3.56	14.50/368.30	4.00/101.60	—	30/133.40	100	1,000
TY525M	TY25M	.19/4.83	7.31/185.67	1.75/44.45	MS3957-1	50/222.40	100	1,000
TY5253M	TY253M	.19/4.83	11.60/294.64	3.00/76.20	MS3957-7	50/222.40	100	1,000
TY528M	TY28M	.19/4.83	14.20/360.68	4.00/101.60	MS3957-2	50/222.40	100	1,000
TY5272M*	TY272M*	.27/6.86	8.75/222.250	2.00/50.80	—	120/533.80	50	500
TY527M*	TY27M*	.27/6.86	13.40/340.36	3.50/88.90	MS3957-3	120/533.80	50	500
TY5275M	TY275M	.27/6.86	18.00/457.20	5.00/127.00	—	120/533.80	50	500
TY5277M	TY277M	.27/6.86	24.30/617.22	7.00/177.80	—	120/533.80	50	500
TY529M	TY29M	.27/6.86	30.00/762.00	9.00/228.60	MS3957-6	120/533.80	50	500
TY53510M*	—	.32/8.13	35.00/889.00	10.00/254.00	—	175/778.40	50	—
TY54513M*	—	.32/8.13	45.00/1143.00	13.00/330.20	—	175/778.40	50	—

Cable ties made from natural nylon 6.6 are excellent performers in most applications.

For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

† UL, SP Recognized Models

• UL Listed Natural 6.6 Nylon Cable Ties are suitable for use in air bending spaces (plenums) in accordance with Section 300.22 (C) & (D) of the National Electrical Code.

• Natural nylon color

The colors you need in convenient packs!

Ty-Rap® Nylon 6.6 Cable Ties — Color Assortment



- Construction — nylon 6.6, 316 stainless steel locking device



STD. PKG. CAT. NO.	BULK PKG. CAT. NO.	DESCRIPTION	LENGTH IN./MM	TENSILE STRENGTH LBS./N.	STD. BULK QTY.
—	TY525M-CLRS	Multi-Colored, Natural Nylon, (10 each of standard ten colors)	7.31/185.67	50/222.40	100 Ties
—	TY25M-0	Black, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-1	Brown, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-2	Red, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-3	Orange, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-4	Yellow, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-5	Green, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-6	Blue, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-7	Purple, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-8	Gray, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties
—	TY25M-9	White, Natural Nylon	7.31/185.67	50/222.40	1,000 Ties

For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

- UL Listed Natural 6.6 Nylon Cable Ties are suitable for use in air bending spaces (plenums) in accordance with Section 300.22 (C) & (D) of the National Electrical Code.

- 100 standard ties in black, brown, red, orange, yellow, green, blue, purple, gray, and white (10 each)

- Recommended tooling — ERG-50, W71-TB

Natural nylon is standard. For colored Ty-Rap® ties, add the following suffix numbers to catalog numbers.

Example: TY25M-2 would be red TY25M. (Consult customer service for ordering information.)

COLOR	SUFFIX NO.	COLOR	SUFFIX NO.	COLOR	SUFFIX NO.	COLOR	SUFFIX NO.
Black	X	Red	2	Green	5	Gray	8
(outdoor)		Orange	3	Blue	6	White	9
Brown	1	Yellow	4	Purple	7		

How to Order Colored Ty-Rap® Cable Ties and Accessories