





PCB Modular Jacks

154-7623PCB, 154-UL623-4PCB, 154-UL623-6PCB




PCB Modular Jacks


154-7623PCB, 154-UL623-4PCB, 154-UL623-6PCB



PCB Layout
(6 Contact)



PCB Layout
(4 Contact)



Dimensions: In.

SPECIFICATIONS	
Type:	PC mount
Western electric type:	623PCB; for telephone to wall use
Insulation resistance:	10MΩ
Contact resistance:	20mΩ
Dielectric withstanding voltage:	1000VAC RMS 60Hz
Contact:	ø0.018"
Current rating:	1.5A
Breakdown voltage:	500VAC for 1 minute
Insertion force:	500g ~ 750g
Retention strength:	7.7kgs (jack~pug)
Color:	gray
Glass filled nylon	

MOUSER STOCK NO.	USOC Type	Positions/ Contacts	Gold Plated Contacts
154-7623PCB	RJ12	6/6	3 micron
154-UL623-4PCB	RJ11	6/4	50 micron
154-UL623-6PCB	RJ12	6/6	50 micron

Date Last Revised: 5-22-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300620

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[154-UL623-6PCB](#) [154-UL623-4PCB](#) [154-7623PCB](#)