

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300390391](#)
Status: **Active**
Overview: [DeviceNet Solutions](#)
Description: DeviceNet Power Tap Splitter, 5 Pole Male, Straight to 2-5 Pole Female

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


Agency Certification	
UL	E152210
General	
Product Family	Industrial Tees and Splitters
Series	130039
IP Rating	IP67
Overview	DeviceNet Solutions
Product Name	DeviceNet Trunk
Type	Power Tap Tee
UPC	78678842591

Physical	
Color - Cable Jacket	Gray
Drop Connector	DeviceNet
Drop Gender	Male
Keyway	Single
LED Indicator	No
Left Trunk Connector	DeviceNet
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PBT
Material - Coupling Nut	Die-Cast Zinc
Poles	5
Right Trunk Connector	DeviceNet
Right Trunk Gender	Female
Temperature Range - Operating	-20°C to +105°C

Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	50V DC

Material Info	
Engineering Number	DN-PT2

Reference - Drawing Numbers	
Sales Drawing	SD-130039-038



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130039](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION