



Sample photo

Order symbol: PCM 175/60 G
Product nbr: 6016319
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074038111
El. number:
Finland: 3421645
Denmark: 8212027226
Italy: 7341060
Sweden: 2535336
Norway: 2535525

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		180	180	60	Ingress Protection (EN 60529): IP 66/67
inch:		7.1	7.1	2.4	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Gasket material:		TPE			Certificates:
Temperatures:					Germanischer Lloyd (GL)
Short term:		-40 ... 120 °C			Underwriters Laboratories
Continuous:		-40 ... 80 °C			Det Norske Veritas
Short term:		-40 ... 250 °F			Fimko
Continuous:		-40 ... 175 °F			Europe EN 62208: 2003
Accessories:					UL Canada
MIV 175		Mounting plate (Galvanized steel)			Gost R
MIN 15		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP A 175/180		Front plate (Aluminium)			
HFP 180		Front plate hinge series			
FP 22046		Wall fastening lug (4 pcs)			

