



English | 简体中文 | 日本語

Search Entire Site [GO](#)

[Contact IDT](#) | [Investors](#) | [Press](#)

[About IDT](#)

[Products](#)

[Applications](#)

[Support](#)

[myIDT](#)

[Document Search](#) | [Package Search](#) | [Parametric Search](#) | [Cross Reference Search](#) | [Green & RoHS](#) | [Calculators](#) | [Thermal Data](#) | [Reliability & Quality](#) | [Military](#)

[Home](#) > [Products](#) > > [97U2A844A](#) > [97U2A844AHLF](#)

[Add to myIDT \[?\]](#)

You may also like...

97U2A844AHLF

Category:

Generic Part:

Market Group:

Description:

[97U2A844A](#)

RDIMM

ICS

**Time is
money**

Parameters

Package	CABGA 28 (ADG28)
Speed	NA
Temperature	C
Voltage	5.0 V
Status	New
Sample	No
Minimum Order Quantity	1
Factory Order Increment	1

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

No documents available for this part at this time.

Package

Description	BGA 4.0MM 4.5MM, 28BALL
Class	PLASTIC
Moisture Sensitivity Level (MSL)	3
Category	Green
Moisture Exposure Floor Life	168 hrs. @ <30°C/60% RH
Peak Reflow Temperature	260°C
Rebake Conditions	48 hrs.@125°C
Length	4.5
Mark	H
Width	4.0
Pitch	0.65
Thickness	1.0
Status	Active

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) What is this?

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. [All Rights Reserved](#).