

Sales Outline Drawing

Revision A


Specifications:

Oscillation Frequency (Hz)	2600 \pm 200
Operating Voltage (Vp-p)	1.1 ~ 3.0
Rated Voltage (Vp-p)	1.5
Current Consumption Max. (mA)	30 at Rated Voltage
Sound Pressure Level (dB/min)	85 at 10cm at Rated Voltage
Coil Resistance (Ω)	15 \pm 3
Operating Temperature ($^{\circ}$ C)	-30 ~ +70
Storage Temperature ($^{\circ}$ C)	-40 ~ +80
Lead Pin	Tin Plated Brass
Housing	PPO plastic resin (Color : Black)
Weight (Grams)	1.6
Condition by wave soldering ($^{\circ}$ C)	245 \pm 5 / 3 \pm 0.5 sec
Condition by hand soldering ($^{\circ}$ C)	350 \pm 20 / within 5 sec
Options	For other options contact factory


PS: Vp-p = 1/2duty, square wave

RoHS Compliant

Dimensions: (units: mm)



Recommended Driving Circuit:



The base current I_b should be high enough so that it saturates the collector current of the transistor with the CB load.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PB-1226PEAQ](#)