


RS stock no: 226-1077

BPA

12 V 28 W



Nominal voltage	U_N	12 V
Nominal output	P_N	28 W
Nominal current	I_N	5 A
Nominal speed	n_N	4500 min ⁻¹
Continuous torque	M_D	6 N · cm
Tightening torque	M_A	35 N · cm
Direction of rotation		R
Type of duty		S1
Degree of protection		IP 10
Weight		0.38 kg
Diagram		b
Part number		0 130 007 027




RS stock no: 226-1083



24 V 25 W

Nominal voltage	U_N	24 V
Nominal output	P_N	25 W
Nominal current	I_N	2.5 A
Nominal speed	n_N	4000 min ⁻¹
Continuous torque	M_D	6 N · cm
Tightening torque	M_A	40 N · cm
Direction of rotation		R
Type of duty		S1
Degree of protection		IP 10
Weight		approx. 0.363 kg
Diagram		b
Part number		0 130 007 051








RS stock no: 226-1077



- A (-) Receptacle for blade terminal 6.3 x 0.8
 B (+) Blade terminal 6.3 x 0.8



RS stock no: 226-1083



- A (-) Receptacle for blade terminal 6.3 x 0.8
 B (+) Blade terminal 6.3 x 0.8