


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECO-13-017507	08NOV2013	KH	MB



D

D



WIRE ENTRY

CLAMPING SCREW



RETENTION LATCH

6.25 REF


C

C

B

B

MATING FACE



POLARIZATION KEY SLOT

2.5 REF
TYP


5.00±0.05
TYP




SEE DETAIL N	TIN PLATED	30	6	3-284040-6
SEE DETAIL M	TIN PLATED	110	22	3-284040-2
-	4	25	5	2-284040-6
-		125	25	2-284040-5
-		120	24	2-284040-4
-		115	23	2-284040-3
-		110	22	2-284040-2
-		105	21	2-284040-1
-		100	20	2-284040-0
-		95	19	1-284040-9
-		90	18	1-284040-8
-		85	17	1-284040-7
-		80	16	1-284040-6
-		75	15	1-284040-5
-		70	14	1-284040-4
-		65	13	1-284040-3
-		60	12	1-284040-2
-		55	11	1-284040-1
-		50	10	1-284040-0
-		45	9	284040-9
-		40	8	284040-8
-		35	7	284040-7
-		30	6	284040-6
-		25	5	284040-5
-		20	4	284040-4
-		15	3	284040-3
-		10	2	284040-2
MARKING	CONTACT FINISH	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 03SEP2002	 TE Connectivity	
DIMENSIONS: mm		CHK C. RICHARD 03SEP2002		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. RICHARD 03SEP2002		
0 PLC ±.3 1 PLC ±.25 2 PLC ±.25 3 PLC ±.25 4 PLC ±.25 ANGLES ±2		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		
MATERIAL 	FINISH 	CUSTOMER DRAWING	NAME TERMINAL BLOCK VERTICAL PLUG STACKING LEFT HAND 5.0mm PITCH	RESTRICTED TO -
		SIZE A3	CAGE CODE 00779	DRAWING NO C-284040
		SCALE 3:1	SHEET 1 OF 2	REV C2

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



DETAIL N
SCALE 2:1



DETAIL M
SCALE 2:1



- 1

MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
CONTACT SPRING : PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2.

WIRE SIZE RANGE: 12 - 30 AWG
- 3

NOT CUMULATIVE TOLERANCE.
- 4

0.00076[.000030] SELECTIVELY GOLD PLATED.
- 5

INK MARKING: WHITE COLOR
NUMERICAL SEQUENCE: FROM LEFT TO RIGHT.
- 6

MECHANICAL CHARACTERISTICS:
INSERTION FORCE: MAX 3N PER POLE
WITHDRAWL FORCE: MIN 1.5N PER POLE
- 7

ELECTRICAL CHARACTERISTICS:
LISTED UNDER UL E60677
VOLTAGE RATING: 300 VOLTS (MAX)
AMPERAGE RATING: 15 AMPS (MAX)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

FINISH
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±°
1 PLC ±.3
2 PLC ±.25
3 PLC ±°
4 PLC ±°
ANGLES ±2

DWN
S.WELDON 03SEP2002

CHK
C.RICHARD 03SEP2002

APVD
C.RICHARD 03SEP2002

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK VERTICAL PLUG
STACKING LEFT HAND
5.0mm PITCH

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-284040

RESTRICTED TO
-

SCALE
3:1

SHEET
2 OF 2

REV
C2

1470-19 (3/13)