


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE	COLOR CODE	DIMENSIONS in.[mm]		INSTALLATION TOOL
			A $\pm .03$ [0,8]	B	
BSK18	22-18	RED	1.12 [28,45]	.136 [3,45]	CT-400
BSK14	16-14	BLUE	1.12 [28,45]	.162 [4,11]	CT-400, CT-460
BSK10 cULus LISTED 587H E52164	12-10	YELLOW	1.24 [31,50]	.225 [5,72]	CT-460



NOTE:


- BSK10: cULus LISTED FOR US AND CANADA
 - 600V MAX. VOLTAGE RATING
 - 302°F (150°C) MAX. TEMP. RATING
 - SOLID, STRANDED, AND INTERNAL (CLASS K) COPPER WIRE
- MATERIAL:
 - STAMPING (22-18 & 16-14) - .03" THK COPPER, TIN PLATED
 - STAMPING (12-10) - .04" THK COPPER, TIN PLATED
 - METAL SLEEVES- BRASS, TIN PLATED
 - HOUSING- KYNAR
- DIMENSIONS IN BRACKETS ARE MILLIMETERS
- WIRE STRIP LENGTH: $3/8^{+1/32-0}$ (9.5 $^{+.8-0}$)
- PACKAGE QUANTITY:

SEE www.panduit.com
FOR PART NUMBER SUFFIX DESIGNATION
FOR PACK SIZE
- KYNAR IS A REGISTERED TRADEMARK OF ARKEMA.

							TITLE			
							KYNAR BUTT SPLICES BSK18,BSK14,BSK10			
							CUSTOMER DRAWING			
3	07-02-13	JBN	TMR	RTFI	D. REVISED NOTE #1 AND CHANGED UL LISTED TO BSK10 ONLY	N41754BA-DC	ITEM REVISION NAME		N41754BA/00	
--	---	--	--	--	C. UPDATED UL LOGO	---	DATASET FILE NAME		N41754BA_DC/00D	
2	8-15-12	JAHA	LSM	LCA	B. REMOVE LINE #4 FROM NOTE A. ADDED COLUMN TO TEXT BOX	N41754BA-DC	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
1	05-21-12	JAHA	LSM	LCA	RELEASED TO PRODUCTION	N41754BA-DC				
R	03-01-12	JAHA	LSM		DRAWING RELEASED		DRAWING NUMBER:		A41754	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE
							JAHA	03-01-12	LSM	NONE

PANDUIT

SEE NOTE



THIRD ANGLE
PROJECTION

SHT 1 OF 1

A