

KLIPPON STB 3 MS HT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



Ideally suited for the energy and process industry and transportation, the Klippon® STB series is the perfect complement to our existing Klippon housing product line. Enclosures of this series comply with international standards such as EN 62208 and EN 60079-0/7 (ATEX).

Features:

- Comes with a standard seal that is resistant to high temperatures (with an extended temperature range of -50°C to +120°C)
- Flexible options when mounting the internal rail
- The seal is protected against compression; this ensures that a permanent and secure seal is maintained.
- Earth stud in housing cover and bottom section
- Lasered welding seams offer improved quality
- Delivered with welded-on mounting to ensure an optimal housing installation

Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

Order No.	1025020000
Part designation	KLIPPON STB 3 MS HT
Version	Enclosures, Sheet steel, 190 mm, 100 mm, 190 mm
GTIN (EAN)	4032248745234
Qty.	1 pc(s).

KLIPPON STB 3 MS HT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Earth, enclosure, cover

Earth, housing, cover	Welded-on M6 x 12 stainless-steel bolts
-----------------------	---

Earth, enclosure, internal

Earth, housing, internal	Welded-on M6 x 16 stainless-steel bolts
--------------------------	---

Earthing enclosure, external

Earth, housing, external	Welded-on M6 x 16 stainless-steel bolts
--------------------------	---

Dimensions

Length	100 mm	Width	190 mm
Height	190 mm	Fixing dimension, width	219 mm
Weight	2,590 g		

General information

Fixing dimension, width	219 mm	Material	Sheet steel
Material thickness	1.5 mm	Surface	lacquered
Colour code		Cover fixing	M5 hexagon stainless-steel slotted screw with 10mm spanner width
	RAL 7032		
Enclosure fixing	Welded-on mounting foot with 8-mm holes	Integral fixing	TAS 20 rail welded to floor
Material	Sheet steel	Material thickness	1.5 mm
Resistance to shocks	10 J version standard	Sealing material	Silicone
Surface	lacquered		

Cable glands top/bottom

M 12	21	M 16	15
M 40	3	M 50	2
M 63	1	M20	10
M25	8	M32	3

cable glands, left

M 12 (3)	21	M 16 (3)	15
M 20 (3)	10	M 25 (3)	8
M 32 (3)	3	M 40 (3)	3
M 50 (3)	2	M 63 (3)	1

cable glands, right

M 12 (2)	21	M 16 (2)	15
M 20 (2)	8	M 25 (2)	6
M 32 (2)	3	M 40 (2)	2
M 50 (2)	1		

KLIPPON STB 3 MS HT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com**Technical data****vertical assembly**

WDU 10 / ZDU 10 (2)	15	WDU 16 / ZDU 16 (2)	13
WDU 4 / ZDU 4 (2)	1x25	WDU 6 / ZDU 6 (2)	1x20

Approvals

Approvals institutes

Classifications

eClass 6.0 27-14-91-07