



40mm sq.**San Ace 40L****General Specifications**

- Material.....Frame: Aluminum, Impeller: Plastics (Flammability: UL94V-0)
- Expected LifeRefer to specifications (L10:Survival rate: 90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire⊕red ⊖black (Sensor) yellow
- Storage Temperature ...-30°C to +70°C (Non-condensing)

40×40×28mm (Mass : 55g) **9L type** **Specifications** The following nos. **have pulse sensors.**

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m ³ /min] [CFM]		Max. Static Pressure [Pa] [inchH ₂ O]		SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
9L0412J301	12	10.2 to 13.8	0.31	3.72	11,700	0.52	18.4	206	0.827	48	-20 to +70	100,000/60°C
9L0412H301			0.15	1.80	8,400	0.37	13.1	106	0.426	40		
9L0412M301			0.045	0.54	4,000	0.16	5.65	24	0.096	19		

Other sensor specifications are available as options. Please refer to the index (p. 509).

Dimensions (unit: mm)**Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[9L0412H302](#) [9L0412M3D01](#) [9L0412M302](#) [9L0412J302](#) [9L0412H3D01](#) [9L0412J3D01](#)