


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART NUMBER | STUD<br>SIZE | DIMENSIONS - in. |              |              |               |              | TOOLS                                                                      |
|------------------------|--------------|------------------|--------------|--------------|---------------|--------------|----------------------------------------------------------------------------|
|                        |              | L<br>± .03       | W<br>± .01   | C<br>± .02   | M<br>± .03    | H<br>± .01   |                                                                            |
| EV18-6LFB              | #6           | .90<br>(22.9)    | .27<br>(6.9) | .22<br>(5.6) | .68<br>(17.3) | .14<br>(3.6) | *CT-100A<br>CT-600A (CT-500CH)<br>CT-600A (CT-550CH)<br>CT-1550<br>CT-1551 |
| EV18-8LFB              | #8           | .97<br>(24.6)    | .29<br>(7.4) | .25<br>(6.4) | .73<br>(18.5) | .16<br>(4.1) |                                                                            |
| EV18-10LFB             | #10          | .97<br>(24.6)    | .33<br>(8.4) | .25<br>(6.4) | .73<br>(18.5) | .19<br>(4.8) |                                                                            |

\*CT-100A, 167°F (75°C) MAX TEMP. RATING

#### NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
  - #22-18 AWG STRANDED COPPER WIRE
  - 221°F (105°C) MAX TEMP RATING
  - 600V MAX VOLTAGE RATING  
(1000V. MAX. IN SIGNS, FIXTURES & LUMINARIES)
- MATERIAL:
  - STAMPING - .032" (.81) THK, COPPER TIN PLATED
  - HOUSING - VINYL, RED
- WIRE STRIP LENGTH: 5/16"  $\begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$  (7.9mm  $\begin{smallmatrix} +0.8 \\ -0 \end{smallmatrix}$ )
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS



|                                                                    |      |                                                                              |       |
|--------------------------------------------------------------------|------|------------------------------------------------------------------------------|-------|
| TITLE                                                              |      | STRONGHOLD LOCKING FORK TERMINALS<br>VINYL INSULATED, BUTTED SEAM #22-18 AWG |       |
| ITEM REVISION NAME                                                 |      | CUSTOMER DRAWING                                                             |       |
| DATASET FILE NAME                                                  |      | 00123SHV/00                                                                  |       |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN (mm) |      | MATERIAL:                                                                    |       |
| .X ±<br>.XX ±                                                      |      | SEE NOTES                                                                    |       |
| .XXX ±<br>ANGLES ±                                                 |      | DRAWING NUMBER:                                                              |       |
| THIRD ANGLE<br>PROJECTION                                          |      | SH41288                                                                      |       |
| DRAWN BY                                                           | DATE | CHK                                                                          | SCALE |
| JHNU                                                               | 2/18 | TMR                                                                          | NONE  |
| SHT 1 OF 1                                                         |      | A                                                                            |       |