




SCPU-17-G-02.00-AMS-AM

SCPE-G-02.00-S-O-NP

## SCPE, SCPU, SCPFE SERIES

# IP68 SEALED USB & ETHERNET PLUGS

Mates with:  
SCRES

## SPECIFICATIONS

For complete specifications  
see [www.samtec.com?SCPE](http://www.samtec.com?SCPE)

### Insulator Material:

Polycarbonate

### Contact Material:

Phosphor Bronze

### Shield Material:

Phosphor Bronze

### Wire:

24 AWG

### Overmold:

PA66 GF13 FR

### Current Rating:

3.8 A per pin (1 pin powered)

### Operating Temp Range:

-40 °C to +70 °C

### RoHS Compliant:


Yes

## DUST CAP

- DCA-17-02

### Note:

Some lengths, styles and  
options are non-standard,  
non-returnable.



## FIELD TERMINATION KIT

- Ethernet Field Termination Kit available for long cable run and small-opening applications so housings can be customer-installed after the runs are complete.
- SCPFE-17-G-01 Series (For cable outside diameter range of 5.00-5.75 mm)
- SCPFE-17-G-02 Series (For cable outside diameter range of 5.75-6.50 mm)

## ALSO AVAILABLE (MOQ REQUIRED)

- Other wire lengths

Mates with:  
SCRUS

## SPECIFICATIONS

For complete specifications  
see [www.samtec.com?SCPU](http://www.samtec.com?SCPU)

### Insulator Material:

Glass Filled Thermoplastic

### Contact Material:

Copper Alloy

### Shield Material:

CRS

### Wire:

20 AWG (Power)

25 AWG (Signal)

28 AWG (Drain)

### Sealed Overmold:

PA66 GF13 FR

### Operating Temp Range:

-20 °C to +75 °C

### RoHS Compliant:

Yes

### Note:

Some lengths, styles and  
options are non-standard,  
non-returnable.

