

home

test & measurement

download

online catalogue T&M

clamp-type test probes

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

sockets

- 2 mm system
- 2 mm safety system
- 4 mm system
- 4 mm safety system

sets

miscellaneous

Search

Search

company

corporate association

location maps

fairs and exhibitions

jobs

home

imprint

contact

terms and conditions

sitemap

Home

sockets

2 mm system

sockets

2 mm system

MBI 1

search

Search..

Messetermine

No events

MBI 1

datasheet for MBI 1

article number: 930308106



View Full-Size Image

product description:

description:

2 mm diameter miniature socket, insulated, tin-plated copper beryllium contact (spring-loaded), with solder connection. Suitable for installation in equipment chassis and switch panels up to a maximum wall thickness of 5 mm.

typ:

MBI 1 grau/grey

system:

2 mm system

order number:

930 308-106

color versions:

technical data

type of contact:

spring loaded socket

type of termination:

solder

rated voltage:

DC 60 V

rated current:

6 A

contact resistance:

6 mOhm

mounting:

screw

material

contact material:

copper beryllium

contact surface material:

tin-plated

housing material:

PA

environmental conditions:

temperature range:


-20 °C to +60 °C

flammable class:

housing:

94 HB

drawing



© 2009 www.sks-kontakttechnik.eu

Joomla! is Free Software released under the GNU General Public License.