



Fittings for metallic conduits with plastic coating

- PCS-FM Fixed External Thread, IP54

Fixed external thread, nickel plated brass.

Features and Benefits

- Two-part fitting of shell and body with external thread
- Provides tight, reliable hold of conduit
- Can be secured with locknut



Helaguard PCS-FM Fixed External Thread.

MATERIAL	Nickel Plated Brass (NPB)
Operating Temperature	-100 °C to +300 °C



TYPE	Nominal Ø	Thread Size (metric)	Thread Size (PG)	Min. Bore Size	Length (L)	A/F Body	Thread Length	Pack Cont.	Colour	Article-No.
PCS10-FM-PG7	10	-	PG7	5.6	21.0	13	8.0	10 pcs.	Metal (ML)	166-31010
PCS10-FM-M12	10	M12	-	5.6	21.0	13	8.0	10 pcs.	Metal (ML)	166-31000
PCS12-FM-PG9	12	-	PG9	8.5	23.0	17	8.0	10 pcs.	Metal (ML)	166-31011
PCS12-FM-M16	12	M16	-	8.5	23.0	17	8.0	10 pcs.	Metal (ML)	166-31001
PCS16-FM-PG11	16	-	PG11	11.5	25.0	22	10.0	10 pcs.	Metal (ML)	166-31012
PCS16-FM-M16	16	M16	-	11.5	25.0	20	10.0	10 pcs.	Metal (ML)	166-31002
PCS16-FM-M20	16	M20	-	11.5	25.0	22	10.0	10 pcs.	Metal (ML)	166-31003
PCS20-FM-PG16	20	-	PG16	15.3	26.3	24	10.0	10 pcs.	Metal (ML)	166-31014
PCS20-FM-M20	20	M20	-	15.3	26.3	24	10.0	10 pcs.	Metal (ML)	166-31004
PCS25-FM-PG21	25	-	PG21	19.1	32.5	29	12.0	10 pcs.	Metal (ML)	166-31015
PCS25-FM-M25	25	M25	-	19.1	32.5	29	10.0	10 pcs.	Metal (ML)	166-31005
PCS32-FM-PG29	32	-	PG29	26.2	36.8	38	13.0	2 pcs.	Metal (ML)	166-31016
PCS32-FM-M32	32	M32	-	26.2	36.8	36	13.0	2 pcs.	Metal (ML)	166-31006
PCS40-FM-PG36	40	-	PG36	34.2	39.0	48	14.0	2 pcs.	Metal (ML)	166-31017
PCS40-FM-M40	40	M40	-	34.6	39.0	48	14.0	2 pcs.	Metal (ML)	166-31007
PCS50-FM-PG42	50	-	PG42	44.8	42.0	58	15.0	1 EA	Metal (ML)	166-31018
PCS50-FM-M50	50	M50	-	44.7	42.0	58	15.0	1 EA	Metal (ML)	166-31008
PCS63-FM-M63	63	M63	-	54.5	50.0	70	18.0	1 EA	Metal (ML)	166-31009
PCS75-FM-M75	75	M75	-	66.5	60.0	84	20.0	1 EA	Metal (ML)	166-31019

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.