



About

Ne

Conta

Empl

Site

H

keyword search:

part number search:

Products

Support

Requests

Investors

SAB18 (#14700)

RFQ/Sample

Transient Voltage Suppressor

Package

Division

Scottsdale

Datasheet

(none)

Mil-Spec

(none)

Shipping

TR12\4000cntTR12

Qual Data

Contact Microsemi

Config

? Unidirectional

Maximum Electrical Rating	Symbol	Max	Unit
Peak Pulse Power			
(Ipp=16.3 A,10/1000µ s pulse)	P _{pp}	500	W
Max Stand -Off/Working Voltage	V _{wm}	18	V
Tolerance	Tol	5	%

Electrical Rating	Symbol	Min	Typ	Max	Unit
Clamping Voltage					
(Ipp=16.3 A)	V _C			30.5	V
Reverse Breakdown Voltage					
(I _{BR} =1000 µ A)	V _{BR}	20.4			V
Reverse Leakage Current					
(Vwm=18 V)	I _D			2	µ A

