




Drawing Number	Part Number	Contact No. (A)	Wire Specification (B)			Wire Specification Ins O/D	Terminal Specification Ins O/D	Wire Length (C)	Associated Connector System
			Wire size	Wire Colour	Wire type				
JUKMH-513-00	01SZHSZH-30L150	SZH-003T-P0.5	30 AWG	RED	UL1571	0.70 mm	0.50 - 0.90 mm	150mm	ZH
JUKMH-514-00	01SZHSZH-30L300	SZH-003T-P0.5	30 AWG	RED	UL1571	0.70 mm	0.50 - 0.90 mm	300mm	ZH
JUKMH-515-00	01SWPRSWPR-24L150	SWPR-001T-P025	24 AWG	BLUE	UL1007	1.42 mm	1.40 - 1.60 mm	150mm	JWPF
JUKMH-516-00	01SWPRSWPR-24L300	SWPR-001T-P025	24 AWG	BLUE	UL1007	1.42 mm	1.40 - 1.60 mm	300mm	JWPF
JUKMH-517-00	01SWPTSWPT-24L150	SWPT-001T-025	24 AWG	BLUE	UL1007	1.42 mm	1.40 - 1.60 mm	150mm	JWPF
JUKMH-518-00	01SWPTSWPT-24L300	SWPT-001T-025	24 AWG	BLUE	UL1007	1.42 mm	1.40 - 1.60 mm	300mm	JWPF
JUKMH-519-00	01SPHSPH-26L150	SPH-002T-P0.5	26 AWG	BLUE	UL1061	0.98 mm	0.90 - 1.50 mm	150mm	PH
JUKMH-520-00	01SPHSPH-26L300	SPH-002T-P0.5	26 AWG	BLUE	UL1061	0.98 mm	0.90 - 1.50 mm	300mm	PH
JUKMH-521-00	01SXHSXH-26L150	SXH-001T-P0.6	26 AWG	BLUE	UL1061	0.98 mm	0.90 - 1.50 mm	150mm	XH
JUKMH-522-00	01SXHSXH-26L300	SXH-001T-P0.6	26 AWG	BLUE	UL1061	0.98 mm	0.90 - 1.50 mm	300mm	XH
JUKMH-523-00	SXA-SXA-22150	SXA-001T-P0.6	22 AWG	GREY	UL1007	1.56 mm	1.20 - 1.90 mm	150mm	XA
JUKMH-524-00	SXA-SXA-22300	SXA-001T-P0.6	22 AWG	GREY	UL1007	1.56 mm	1.20 - 1.90 mm	300mm	XA

JUKMH-525-00	01SYMSYM-26L150	SYM-001T-P0.6	26 AWG	BLUE	UL1007	1.28 mm	1.20 - 1.80 mm	150mm	SM and RCY
JUKMH-526-00	01SYMSYM-26L300	SYM-001T-P0.6	26 AWG	BLUE	UL1007	1.28 mm	1.20 - 1.80 mm	300mm	SM and RCY
JUKMH-527-00	01SHFSHF-26L150	SHF-001T-0.8BS	26 AWG	BLUE	UL1007	1.28 mm	1.20 - 1.80 mm	150mm	SM
JUKMH-528-00	01SHFSHF-26L300	SHF-001T-0.8BS	26 AWG	BLUE	UL1007	1.28 mm	1.20 - 1.80 mm	300mm	SM
JUKMH-529-00	01SYFSYF-26L150	SYF-001T-P0.6	26 AWG	BLUE	UL1007	1.28 mm	1.20 - 1.80 mm	150mm	RCY
JUKMH-530-00	01SYFSYF-26L300	SYF-001T-P0.6	26 AWG	BLUE	UL1007	1.28 mm	1.20 - 1.80 mm	300mm	RCY
JUKMH-531-00	01SVHSHVH-20L150	SVH-21T-P1.1	20 AWG	WHITE	UL1007	1.73 mm	1.70 - 3.0 mm	150mm	VH
JUKMH-532-00	01SVHSHVH-20L300	SVH-21T-P1.1	20 AWG	WHITE	UL1007	1.73 mm	1.70 - 3.0 mm	300mm	VH
JUKMH-533-00	01SVMSVM-18L150	SVM-61T-P2.0	18 AWG	BLACK	UL1015	2.80 mm	1.90 - 3.40 mm	150mm	VL
JUKMH-534-00	01SVMSVM-18L300	SVM-61T-P2.0	18 AWG	BLACK	UL1015	2.80 mm	1.90 - 3.40 mm	300mm	VL
JUKMH-535-00	01SVFSVF-18L150	SVF-61T-P2.0	18 AWG	BLACK	UL1015	2.80 mm	1.90 - 3.40 mm	150mm	VL
JUKMH-536-00	01SVFSVF-18L300	SVF-61T-P2.0	18 AWG	BLACK	UL1015	2.80 mm	1.90 - 3.40 mm	300mm	VL
JUKMH-537-00	01SWPJRSWPJR-20L150	SWPJ-21T-M0.5	20 AWG	WHITE	UL1015	2.51 mm	2.32 - 2.83 mm	150mm	WPJ
JUKMH-538-00	01SWPJRSWPJR-20L300	SWPJ-21T-M0.5	20 AWG	WHITE	UL1015	2.51 mm	2.32 - 2.83 mm	300mm	WPJ
JUKMH-539-00	01SLCSLC-20L150	SLC-21T-2.0	20 AWG	WHITE	UL1007	1.73 mm	1.70 - 2.10 mm	150mm	LC
JUKMH-540-00	01SLCSLC-20L300	SLC-21T-2.0	20 AWG	WHITE	UL1007	1.73 mm	1.70 - 2.10 mm	300mm	LC
JUKMH-541-00	01SXAMSXAM-26L150	SXAM-001T-P0.6	26 AWG	BLUE	UL1007	1.28 mm	1.20 -1.90 mm	150mm	XA (w to w)
JUKMH-542-00	01SXAMSXAM-26L300	SXAM-001T-P0.6	26 AWG	BLUE	UL1007	1.28 mm	1.20 -1.90 mm	300mm	XA (w to w)
JUKMH-543-00	01SLEBSLEB-26L150	SLEB-001T-P0.2	26 AWG	BLUE	UL1061	0.98 mm	0.95 - 1.30 mm	150mm	LEB
JUKMH-544-00	01SLEBSLEB-26L300	SLEB-001T-P0.2	26 AWG	BLUE	UL1061	0.98 mm	0.95 - 1.30 mm	300mm	LEB
JUKMH-545-00	01SEHSEH-22150	SEH-001T-P0.6	22 AWG	GREY	UL1007	1.56 mm	1.00 - 1.90 mm	150mm	EH
JUKMH-546-00	01SEHSEH-22300	SEH-001T-P0.6	22 AWG	GREY	UL1007	1.56 mm	1.00 - 1.90 mm	300mm	EH