

[illegible]

1.27μm MIN NICKEL UNDERPLATING

NB OF POS PER ROW : 02 TO 25

STYLE	POST LENGTH ±0.2
51	2.00
52	4.00
53	3.50
54	2.50

5. PACKAGING:

K = TAPE AND REEL WITHOUT CAP. SEE TA884 FOR AVAILABILITY.

6. FOR POLARIZATION, SPECIFY POSITION NUMBER TO OMIT PIN.
EXAMPLE : 03 = OMIT PIN POSITION 3, SEE TOP VIEW.
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.

7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2μm MINIMUM MATTE TIN OVER 1.27μm MINIMUM NICKEL UNDERPLATE.


b – MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDES IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

c - LABELLING:




– MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT : SEE GS-47-0004



Technical drawing of a rectangular plate with the following dimensions and labels:

- Overall width: $(N \times 2.00)$
- Overall height: 2.00
- Top flange thickness: 1.00
- Bottom flange thickness: $1.00 \pm 0.3(x2)$
- Central section width: 4.00
- Labels: POS 3, POS 1, POS 2, POS 4
- Note: NOTE 3

[illegible]