FITTINGS HAZ LOC

GU/UN SERIES

UNIONS

GUF-2

GUF-8

GUM-2

GUML-2

UNF2

Female to Female

UNY4 UNY2

Male to Female

GUML-2M

90° Elbow Union

- GUF/GUM/UNF/UNY 1/2", 3/4", & 1"
  Class I, Div. 1 & 2, Groups A,B,C,D
  Class I, Zone I, IIC, IIB, IIA
  Class I, Zone 1, Groups IIC, IIB, IIA
  Class II, Div. 1 & 2, Groups E,F,G
  Class III
- GUF/GUM/UNF/UNY 1-1/4" through 4"
  Class I, Div. 1 & 2, Groups C,D
  Class I, Zone I, IIB, IIA
  Class I, Zone 1, Groups IIB, IIA
  Class II, Div. 1 & 2, Groups E,F,G
  Class III

UL LISTED File No. E 10514

SP Certified File No. LR11716

FEATURES-SPECIFICATIONS

Applications

- GUF/GUM or UNF/UNY unions are used to connect two pieces of conduit or attach conduit to junction boxes, fittings, or devices
- Permits removal of equipment without turning or removal of conduit

Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction

Material/Finish

Copper-free Aluminum
(less than 4/10 of 1%)

- Natural Finish
- 1/2" - 2" screw machine
- 2-1/2" - 4" cast

Iron – 1-1/4"- 4"

Steel – 1/2", 3/4", 1"

- Zinc electro-plate

Third-Party Standards

UL Standards 886 and 1203
CSA Standard C22.2 No. 30

For ATEX and IEC Ex certified Unions, see following page.

FEMALE TO FEMALE

CAT. NO. KILLARK ALUM.	HUB SIZE	DIMENSIONS A DIAMETER	DIMENSIONS B LENGTH	CAT. NO. STEEL/ IRON	HUB SIZE	DIMENSIONS A DIAMETER	DIMENSIONS B LENGTH
GUF-1①	1/2"	1-7/16"(37)	1-7/8"(48)	UNF1①	1/2"	1-1/2"(37)	1-55/64"(47)
GUF-2①	3/4"	1-5/8"(41)	1-15/16"(49)	UNF2①	3/4"	1-3/4"(45)	1-59/64"(49)
GUF-3①	1"	2"(51)	2-29/64"(62)	UNF3①	1"	2"(51)	2-7/16"(62)
GUF-4	1-1/4"	2-3/8"(60)	2-1/2"(63)	UNF4	1-1/4"	2-27/32"(72)	2-1/4"(57)
GUF-5	1-1/2"	2-5/8"(67)	2-1/2"(63)	UNF5	1-1/2"	3-3/32"(79)	2-7/16"(62)
GUF-6	2"	3-1/4"(82)	2-5/8"(67)	UNF6	2"	3-3/4"(95)	2-5/8"(67)
GUF-7	2-1/2"	4-1/2"(114)	3"(76)	UNF7	2-1/2"	4-1/2"(114)	3"(76)
GUF-8	3"	5-3/8"(136)	3-1/16"(78)	UNF8	3"	5-3/8"(136)	3-1/16"(78)
GUF-9	3-1/2"	6-1/4"(159)	3-9/16"(90)	UNF9	3-1/2"	6-1/4"(159)	3-9/16"(90)
GUF-0	4"	6-1/4"(159)	3-9/16"(90)	UNF0	4"	6-1/4"(159)	3-9/16"(90)
MALE TO FEMALE							
GUM-1①	1/2"	1-7/16"(37)	2-1/2"(64)	UNY1①	1/2"	1-1/2"(37)	2-9/16"(65)
GUM-2①	3/4"	1-5/8"(41)	2-9/16"(65)	UNY2①	3/4"	1-3/4"(45)	2-5/8"(67)
GUM-3①	1"	2"(51)	3-3/64"(77)	UNY3①	1"	2-1/32"(52)	3-5/64"(78)
GUM-4	1-1/4"	2-3/8"(60)	3-1/4"(83)	UNY4	1-1/4"	2-15/16"(75)	3-1/4"(83)
GUM-5	1-1/2"	2-5/8"(67)	3-1/4"(83)	UNY5	1-1/2"	3-3/16"(81)	3-1/2"(89)
GUM-6	2"	3-1/4"(82)	3-5/8"(92)	UNY6	2"	3-3/4"(95)	4"(102)
GUM-7	2-1/2"	4-1/2"(114)	4-15/16"(125)	UNY7	2-1/2"	4-1/2"(114)	4-15/16"(125)
GUM-8	3"	5-3/8"(136)	5-7/32"(133)	UNY8	3"	5-3/8"(133)	5-7/32"(133)
GUM-9	3-1/2"	6-1/4"(159)	5-13/16"(148)	UNY9	3-1/2"	6-1/4"(159)	5-13/16"(148)
GUM-0	4"	6-1/4"(159)	5-13/16"(148)	UNY0	4"	6-1/4"(159)	5-13/16"(148)

90° ANGLE UNION

CAT. NO. KILLARK ALUM.	HUB SIZE	DIMENSIONS A DIA.	DIMENSIONS B LENGTH	DIMENSIONS C	CAT. NO. STEEL/ IRON	HUB SIZE	DIMENSIONS A DIA.	DIMENSIONS B LENGTH	DIMENSIONS C
GUML-1	1/2"	2-1/2" (64)	1-7/16" (37)	1-3/4" (44)	GUML-1M	1/2"	2-1/4" (32)	1-1/2" (38)	1-5/8" (42)
GUML-2	3/4"	2" (51)	1-5/8" (42)	1-5/8" (42)	GUML-2M	3/4"	2-1/4" (32)	1-3/4" (44)	2" (51)

① UL & CSA suitable for Class I, Groups A, B, C, D.

Dimensions



GUF



UNF



GUM



UNY



GUML

FITTINGS

GU/UN SERIES

UNIONS - ATEX/IEC Ex CERTIFIED

GUF-2 GUF-8

GUM-2

GUML-2

UNF2

Female to Female

UNY4 UNY2

Male to Female

GUML-2M

90° Elbow Union

Global Listings

ATEX / IEC Ex Certified

File nos. CML 16ATEX 1325X
IECEx QPS16.0012X
Ⓔx II2GD
Ex db IIC Gb
Ex tb IIIC Db IP65

UL LISTED File No. E 10514

CSA Certified File No. LR11716

See previous page for UL and CSA suitabilities

FEATURES-SPECIFICATIONS

Applications

- GUF/GUM or UNF/UNY unions are used to connect two pieces of conduit or attach conduit to junction boxes, fittings, or devices
- Permits removal of equipment without turning or removal of conduit

Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction

Material/Finish

Copper-free Aluminum
(less than 4/10 of 1%)

- Natural Finish
- 1/2" - 2" screw machine
- 2-1/2" - 4" cast

Iron – 1-1/4"- 4"

Steel – 1/2", 3/4", 1"

- Zinc electro-plate

Third-Party Standards

UL Standards 886 and 1203
CSA Standard C22.2 No. 30

For NON-ATEX and IEC Ex certified Unions, see previous page.

FEMALE TO FEMALE - QUAD LISTED

CAT. NO. KILLARK ALUM.	HUB SIZE	DIMENSIONS A DIAMETER	DIMENSIONS B LENGTH	CAT. NO. STEEL/ IRON	HUB SIZE	DIMENSIONS A DIAMETER	DIMENSIONS B LENGTH
GUF-1-EX①	1/2"	1-7/16"(37)	1-7/8"(48)	UNF1-EX①	1/2"	1-1/2"(37)	1-55/64"(47)
GUF-2-EX①	3/4"	1-5/8"(41)	1-15/16"(49)	UNF2-EX①	3/4"	1-3/4"(45)	1-59/64"(49)
GUF-3-EX①	1"	2"(51)	2-29/64"(62)	UNF3-EX①	1"	2"(51)	2-7/16"(62)
GUF-4-EX	1-1/4"	2-3/8"(60)	2-1/2"(63)	UNF4-EX	1-1/4"	2-27/32"(72)	2-1/4"(57)
GUF-5-EX	1-1/2"	2-5/8"(67)	2-1/2"(63)	UNF5-EX	1-1/2"	3-3/32"(79)	2-7/16"(62)
GUF-6-EX	2"	3-1/4"(82)	2-5/8"(67)	UNF6-EX	2"	3-3/4"(95)	2-5/8"(67)
GUF-7-EX	2-1/2"	4-1/2"(114)	3"(76)	UNF7-EX	2-1/2"	4-1/2"(114)	3"(76)
GUF-8-EX	3"	5-3/8"(136)	3-1/16"(78)	UNF8-EX	3"	5-3/8"(136)	3-1/16"(78)
GUF-9-EX	3-1/2"	6-1/4"(159)	3-9/16"(90)	UNF9-EX	3-1/2"	6-1/4"(159)	3-9/16"(90)
GUF-0-EX	4"	6-1/4"(159)	3-9/16"(90)	UNF0-EX	4"	6-1/4"(159)	3-9/16"(90)
MALE TO FEMALE - QUAD LISTED							
GUM-1-EX①	1/2"	1-7/16"(37)	2-1/2"(64)	UNY1-EX①	1/2"	1-1/2"(37)	2-9/16"(65)
GUM-2-EX①	3/4"	1-5/8"(41)	2-9/16"(65)	UNY2-EX①	3/4"	1-3/4"(45)	2-5/8"(67)
GUM-3-EX①	1"	2"(51)	3-3/64"(77)	UNY3-EX①	1"	2-1/32"(52)	3-5/64"(78)
GUM-4-EX	1-1/4"	2-3/8"(60)	3-1/4"(83)	UNY4-EX	1-1/4"	2-15/16"(75)	3-1/4"(83)
GUM-5-EX	1-1/2"	2-5/8"(67)	3-1/4"(83)	UNY5-EX	1-1/2"	3-3/16"(81)	3-1/2"(89)
GUM-6-EX	2"	3-1/4"(82)	3-5/8"(92)	UNY6-EX	2"	3-3/4"(95)	4"(102)
GUM-7-EX	2-1/2"	4-1/2"(114)	4-15/16"(125)	UNY7-EX	2-1/2"	4-1/2"(114)	4-15/16"(125)
GUM-8-EX	3"	5-3/8"(136)	5-7/32"(133)	UNY8-EX	3"	5-3/8"(133)	5-7/32"(133)
GUM-9-EX	3-1/2"	6-1/4"(159)	5-13/16"(148)	UNY9-EX	3-1/2"	6-1/4"(159)	5-13/16"(148)
GUM-0-EX	4"	6-1/4"(159)	5-13/16"(148)	UNY0-EX	4"	6-1/4"(159)	5-13/16"(148)

90° ANGLE UNION - QUAD LISTED

CAT. NO. KILLARK ALUM.	HUB SIZE	DIMENSIONS A DIA.	DIMENSIONS B LENGTH	DIMENSIONS C	CAT. NO. STEEL/ IRON	HUB SIZE	DIMENSIONS A DIA.	DIMENSIONS B LENGTH	DIMENSIONS C
GUML-1-EX	1/2"	2-1/2" (64)	1-7/16" (37)	1-3/4" (44)	GUML-1M-EX	1/2"	2-1/4" (32)	1-1/2" (38)	1-5/8" (42)
GUML-2-EX	3/4"	2" (51)	1-5/8" (42)	1-5/8" (42)	GUML-2M-EX	3/4"	2-1/4" (32)	1-3/4" (44)	2" (51)

① *UL & CSA suitable for Class I, Groups A, B, C, D.*

Dimensions



GUF



UNF



GUM



UNY



GUML