



**Product Number: NBF-32006**  
**UL/NEMA/IEC NBF Series – Solid Door Plastic Boxes**



***Design Features***

- Designed to IP66 of IEC 529 and NEMA 1, 2, 4, 4x, 12 and 13 specifications
- All plastic construction including hinge pins
- Comes complete with stainless steel wall mounting brackets and hardware
- Style A has two or 3 plastic latches
- **Indoor Versions:**
  - ABS plastic enclosures are molded out of light gray material with UL94-HB Flammability rating. (Not UL Listed)
  - ABS/PC blended plastic enclosures are molded out of light gray material with UL94-5VA flammability rating. Suggested service temperature range - 40C to +70C.
  - Clear doors, for all models, are molded out of Polycarbonate material with UL94-V0 flammability rating.
- **Outdoor Versions:**
  - PC/PBT blended plastic enclosures are molded out of light gray material with UL94-5VA flammability and UV stabilized

***Nominal External Dimensions Inches (Milimeters):***

- A: 7.87" (200 mm)
- B: 3.93" (100 mm)
- C: 2.75" ( 70 mm)
- D: 1.97" ( 50 mm)

***Actual Internal Dimensions Inches (+/- 0.06):***

- E: 7.31"
- F: 3.42"
- G: 2.52"

***Weight:***

- 0.8 Lbs