

MICRO SWITCHFREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-7RW84-A2

AQJ8400

BZ-7RW84-A2

PAGE 1 OF 1

MDRAWING
NUMBER

7

ISSUE

REPLACES

RELEASE NO. PR-3697

CHECK

REVISIONS

A	MADE EYS	06 JAN 68
B	ORD 22 JAN 68	
C	PR-3697	
D	RER 17 NOV 73	
E	CO-73287-1	
F	JAL 22 NOV 93	
G	CO 77589	
H	TSM 29 MAR 94	
I	CO93346	
J	DLT 20 SEP 98	
K	0017582	
L	TSG 06 JAN 06	

CHECK

68

24

JAN

LSD

CHECK

68

ORD


22

JAN

68

FORMTEK
FO-50378-1A

DRAWN

**NOTE**

⚠ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
.139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE----- 2 OZ MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE----- 1/8 OZ MIN	-L96- 15 A-125, 250, OR 480 VAC 1/2 A-125 VDC; 1/4 A-250 VDC 1/8 HP-125 VAC; 1/4 HP-250 VAC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL---.050-.125	-L288-  05    -L315- 16A 250V ~ T85 5E4	TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES 1° ±.005
OVERTRAVEL----- .219 MIN		WEIGHT .073 LB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-7RW84-A2](#)