


# UK Socket

161-RB0200-E

KOBICONN

UK Socket



Dimensions: mm (in.)

## SPECIFICATIONS

|                               |                       |
|-------------------------------|-----------------------|
| <b>Insulation Resistance:</b> | Over 100MΩ at 500V DC |
| <b>Dielectric Strength:</b>   | 2000V AC 1 Minute     |
| <b>Body Material:</b>         | Thermoplastic         |
| <b>Standard:</b>              | BS-1363-2             |

RoHS Compliant

Date Last Revised: 6-29-12

Available from Mouser Electronics  
1-800-346-6873 / [www.mouser.com](http://www.mouser.com)

KC-301219

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-RB0200-E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-RB0200-E](#)