






10 9 8 7 6 5 4 3 2 1



ITEM	COMPONENT	MATERIAL	FINISH
1	REC SHELL	BRASS	NICKEL PLATED
2	INSERT	PUR	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	WIRES	COPPER/PVC	NONE
5	O-RING	NBR	BLACK
6	O-RING	VITON	RED
7	POTTING MATERIAL	EPOXY	NONE

- 1 brown
2 white
3 blue
4 black
5 green/yellow



POL	MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH
04	1200845154	WR4J20E03C3003	300 ± 10
05	1200845159	WR5J20E03C3003	300 ± 10

VOLTAGE RATING	250V
AMPERAGE RATING	4A
PROTECTION CLASS	IP 67/68/69k
OPERATING TEMPERATURE	-25°C to 90°C
UL CERTIFICATION	FILE NO. E152210
CSA CERTIFICATION	FILE NO. LR6837

ENTER DESCRIPTION EC NO: WEU2010-0417 DRWN:STAUDIGEL 2010/03/08 CHKD:FPACHER 2010/03/09 APPR:FPACHER 2010/03/10	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY NSTAUDIGEL	DATE 2010/03/08	TITLE M12U 4/5P REC FEM FRONT MOUNT PG9				
			4 PLACES	± ---	± ---	CHECKED BY FPACHER	DATE 2010/03/09					
			3 PLACES	± ---	± ---	APPROVED BY FPACHER		DATE 2010/03/09	MOLEX INCORPORATED			
			2 PLACES	± 0.05	± ---							
			1 PLACE	± 0.1	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
1	REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
					SD-120084-030		1 OF 1					