


- 1 FOR $\varnothing 9.53$ [$\varnothing.375$] MAX WIRE INSULATION.
- 2 NOTE DELETED
- 3 MATERIAL: BODY; COPPER PER ASTM B152
INSULATION; NYLON
COLOR; NATURAL
- 4 FINISH: BODY; TIN PL. PER ASTM B545



WIRE RANGE	Listed	LR7189 Certified
22-10 AWG SOLID OR STRANDED	22-10 AWG SOLID OR STRANDED	22-10 AWG SOLID OR STRANDED

1500	TAPE MOUNTED	2-35653-1
1000	LOOSE PIECE	35653
QTY	DESCRIPTION	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F] MAX

VOLTAGE RATING:
300V MAX

CIRCULAR MIL AREA:
1.65-6.64mm² [3248-13100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.20 [.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL

3

DWN
G KRUPER
1/93

CHK
R HERSEY
1/93

APVD
M ELLIS
1/93

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

1500

1000

QTY

TE Connectivity

SPLICE, WIRE, CLOSED END
22-10 AWG

SIZE
A3

CAGE CODE
W2

DRAWING NO
C-35653

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
W3

1470-19 (1/15)