

## TM-238 TM-239 Sealing Gasket



### Characteristic

- (1) Excellent on weather-resistance, cold and heat-resistance, chemical-resistance, acid and alkali.
- (2) No deformation by its structure, small compressive stress.
- (3) Easy to compress.
- (4) Excellent waterproof performance for gaps between rough surfaces and for structure with temperature difference, since it follows the structure flexibly.
- (5) No chemical substance shall come out from the foam while it is heated or compressed.
- (6) Light weight, specific gravity 0.15, and no welding between foams, it is easy to install and store.

### Application

Electric devices / Houses / Facility devices / Vessels / Vehicles / Automobiles / Construction and civil engineering uses, etc.

### Specification

- Heat-resistance ——— -20°C~100°C
- Chemical-resistance ——— Excellent on acid-resistance and alkali-resistance
- Waterproofing ——— Waterproof at 70% and more compression.
- Foam ——— Continuous foaming
- Standard Size ——— Thickness: ——— 5mm to 25mm  
Width: ——— 10mm to 30mm with 5mm step  
Color: ——— Two types, black and gray

### Note

1. Dirt and moisture on the surface to be fixed should be removed before fixing.
2. Adhesive agent should not be used for jointing. It may lower the dustproof and waterproof performances.


### How To Order

TM-238 - 5 - 10  
Model No (Black) Thickness width

And quantity you need

- Ask for a custom made product.

Rapping product: Production can be made for the size within 800mm and less square.



■Size List (Black:TM-238, Gray:TM-239)

| Product No. | A  | B  | TM-238   | TM-239   |
|-------------|----|----|----------|----------|
|             |    |    | Code No. | Code No. |
| 5-10        | 5  | 10 | 6151     | 6181     |
| 5-15        |    | 15 | 6152     | 6182     |
| 5-20        |    | 20 | 6153     | 6183     |
| 5-25        |    | 25 | 6154     | 6184     |
| 5-30        |    | 30 | 6155     | 6185     |
| 8-10        | 8  | 10 | 6156     | 6186     |
| 8-15        |    | 15 | 6157     | 6187     |
| 8-20        |    | 20 | 6158     | 6188     |
| 8-25        |    | 25 | 6159     | 6189     |
| 8-30        | 10 | 30 | 6160     | 6190     |
| 10-10       |    | 10 | 6161     | 6191     |
| 10-15       |    | 15 | 6162     | 6192     |
| 10-20       |    | 20 | 6163     | 6193     |
| 10-25       |    | 25 | 6164     | 6194     |
| 10-30       | 15 | 30 | 6165     | 6195     |
| 15-10       |    | 10 | 6166     | 6196     |
| 15-15       |    | 15 | 6167     | 6197     |
| 15-20       |    | 20 | 6168     | 6198     |
| 15-25       |    | 25 | 6169     | 6199     |
| 15-30       | 20 | 30 | 6170     | 6200     |
| 20-10       |    | 10 | 6171     | 6201     |
| 20-15       |    | 15 | 6172     | 6202     |
| 20-20       |    | 20 | 6173     | 6203     |
| 20-25       |    | 25 | 6174     | 6204     |
| 20-30       | 25 | 30 | 6175     | 6205     |
| 25-10       |    | 10 | 6176     | ※ 6206   |
| 25-15       |    | 15 | 6177     | ※ 6207   |
| 25-20       |    | 20 | 6178     | ※ 6208   |
| 25-25       |    | 25 | 6179     | ※ 6209   |
| 25-30       | 30 | 30 | 6180     | ※ 6210   |

A size for ※marked products are made by adhesion of 20mm width product and 5mm width product.

