

Clamps  
Pro-Clamps



01-0703



01-0716

A new design to meet modern clamping requirements. Available in three ranges with throat depths of 80/110 and 140mm. New handles need 30% less effort to apply the same load and built in passive lock eliminates unwanted jaw movement as well as giving easy positioning around the work piece. New I beam section bars give added strength in use. Pro clamp 'L' have T-bar handles.

490396

| Description | Throat<br>Depth(in) | Capacity<br>(mm) (in) | Order Code | Price Each |
|-------------|---------------------|-----------------------|------------|------------|
| Short       | 3                   | 200 8                 | 138-9050   |            |
| Short       | 3                   | 300 12                | 138-9052   |            |
| Short       | 3                   | 400 16                | 138-9053   |            |
| Short       | 3                   | 600 24                | 138-9054   |            |
| Short       | 3                   | 800 32                | 138-9055   |            |
| Medium      | 4.5                 | 300 12                | 138-9056   |            |
| Medium      | 4.5                 | 400 16                | 138-9057   |            |
| Medium      | 4.5                 | 600 24                | 138-9058   |            |
| Medium      | 4.5                 | 800 32                | 138-9059   |            |
| Medium      | 4.5                 | 1000 40               | 138-9060   |            |
| Large       | 5.5                 | 400 16                | 138-9061   |            |
| Large       | 5.5                 | 600 24                | 138-9062   |            |
| Large       | 5.5                 | 800 32                | 138-9064   |            |
| Large       | 5.5                 | 1000 40               | 138-9065   |            |
| Large       | 5.5                 | 1250 50               | 138-9066   |            |
| Large       | 5.5                 | 1500 60               | 138-9067   |            |