




**Panel Mount Indicator, Non-Relampable
Neon and Incandescent Technology
Mounting Hole, Ø 0.500"**



All dimensions are in inches



**RoHS
COMPLIANT**

Recommended panel thickness: 0.030" to 0.090"

.187 terminals are standard

Storage temperature T_{STG} : -25°C - +80°C
Ambient temperature T_A : -20°C - +60°C
Voltage tolerance V_{OP} : ±10%

Part No.	Lens Color	Voltage	Current mA	Rated Life
Neon 115VAC Series				
WL-1050QC1	Red	105-125VAC	1.5mA	25,000 Hrs
WL-1050QC2	Clear	105-125VAC	1.5mA	25,000 Hrs
WL-1050QC3	Amber	105-125VAC	1.5mA	25,000 Hrs
WL-1050QC4	White	105-125VAC	1.5mA	25,000 Hrs
WL-1052QC5	Green	105-125VAC	1.5mA	25,000 Hrs
Neon 230VAC Series				
WL-1051QC1	Red	208-250VAC	1.5mA	25,000 Hrs
WL-1051QC3	Amber	208-250VAC	1.5mA	25,000 Hrs
WL-1051QC4	White	208-250VAC	1.5mA	25,000 Hrs
WL-1053QC5	Green	208-250VAC	1.5mA	25,000 Hrs
Incandescent 12V Series				
WL-1090QC1-12V	Red	12V-14V	80mA	25,000 Hrs
WL-1090QC3-12V	Amber	12V-14V	80mA	25,000 Hrs
WL-1090QC4-12V	White	12V-14V	80mA	25,000 Hrs
WL-1090QC5-12V	Green	12V-14V	80mA	25,000 Hrs
Incandescent 28V Series				
WL-1090QC1-28V	Red	24V-28V	40mA	25,000 Hrs
WL-1090QC3-28V	Amber	24V-28V	40mA	25,000 Hrs
WL-1090QC4-28V	White	24V-28V	40mA	25,000 Hrs
WL-1090QC5-28V	Green	24V-28V	40mA	25,000 Hrs

Body Material: Nylon, white
Lens Material: Polycarbonate
Bezel Material: Stainless steel
Note: .250 quick connects available upon request

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.
Options: Additional options and lens styles available. Please contact Wamco for more information.

Drawn	SC	03/01/10	Panel Mount Indicators Neon and Incandescent	Datasheet: WL-105XQCX Series WL-1090QCX-XXX Series	Rev: 1
Checked	EB	03/01/10			
Approved	EB	03/02/10			