

PIN STYLE	PRODUCT DIMENSIONS			
	"A" ±0.2	"B" ±0.35	"C" REF	"J" REF
01	5.72	3.05	1.4	12.19
02	5.72	3.7	1.4	12.19
03	8.08	2.93	1.52	14.68
04	6.1	3.2	1.52	12.7
05	7.15	3.05	1.52	13.75
06	5.84	2.83	1.52	12.44
07	10.89	3.05	1.52	17.49

76345-9XXLF	0.2µm Au
76345-8XXLF	0.38µm Au/GXT
76345-7XXLF	
76345-6XXLF	0.76µm PdNi - GOLD FLASH
76345-5XXLF	0.38µm PdNi - GOLD FLASH
76345-4XXLF	
76345-3XXLF	2µm MIN MATTE TIN
76345-2XXLF	1.27µm Au/GXT
76345-1XXLF	0.76µm Au/GXT
PLATING CODE	MINIMUM PLATING THICKNESS OVER 1.27µm MIN

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family BSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title HEADER,DR,RA, WIDE BODY,2.54 mm
L	F10407	JMC	91.05.24	angles	linear		
M	F50646	JMC	95.08.30			scale	dwg no 76345
N	F05-0186	LMU	05.05.31				
P	F06-0207	LMU	06.07.27	dr	J COMPAGNON	95.08.29	sheet 2 of - size A3
R	F08-0148	JCO	08.05.27	engr	JMC	95.08.30	
S	B-19261	LMU	14.10.31	chr			type CUSTOMER Drawing
				appd	JMC	95.08.30	
sheet index	revision sheet						