


FCI  
F03019 DLE 03.01.23

FCI

FCI  
F03019 DLE 03.01.23


F



- NOTES:**
- 1 MATERIAL: BASE AND COVER: 30% GLASS FILLED POLYESTER FLAME RETARDANT PER UL-94-V0 COLOUR GREY STRAIN RELIEF: UNREINFORCED THERMOPLASTIC FLAME RETARDANT PER UL-94-V0 COLOUR GREY CONTACT: PHOSPHOR BRONZE
  - 2 PLATING: 0.76  $\mu$ m Au OVER 1.27  $\mu$ m Ni IN CONTACT AREA REMAINDER OF PRODUCT (IDC PART) 1.5  $\mu$ m TIN LEAD OVER 1.27  $\mu$ m Ni
  - 3 TRIANGLE NOT MOLDED-IN ON 2x2 AND 2x3 POSITIONS WITH CENTRAL KEY
  - 4 COVER IS LOSSE PIECE DELIVERED IN BAG OF 100.
  - 5 DIM PRODUCT WITH COVER IN PRELOAD POSITION 13±0.3.


| CUSTOMER COPY FOR REFERENCE ONLY |          |           |          |                                       |            |               |           |                          |                    |
|----------------------------------|----------|-----------|----------|---------------------------------------|------------|---------------|-----------|--------------------------|--------------------|
| mat'l. code                      |          | SEE NOTES |          | tolerances unless otherwise specified |            | CUSTOMER COPY |           | FCI ELECTRONICS          |                    |
| ltr                              | ec'n no  | dr        | date     | linear                                |            | projection    |           | title                    | www.fciconnect.com |
| F                                | V20539   | OMA       | 92.03.23 |                                       |            |               |           | EURO QUICKIE<br>2 PIECES |                    |
| G                                | F10566   | DLE       | 01.10.24 |                                       |            |               |           |                          |                    |
| H                                | F03019   | DLE       | 03.01.23 | angles                                |            |               |           | product family           | QKIE               |
|                                  |          |           |          | dr                                    | P NIZZI    | 94.02.11      | mm [inch] | code                     | 213                |
|                                  |          |           |          | engn                                  | JM PHAMVAN | 93.03.25      |           | size                     | dwg no             |
|                                  |          |           |          | chr                                   | O MATHEVON | 93.03.25      | scale     | A2                       | 79435              |
|                                  |          |           |          | appd                                  | JM P       | 94.02.10      | 5:1       |                          | sheet              |
| sheet                            | revision | H         | H        |                                       |            |               |           |                          | 1 of 2             |
| index                            | sheet    | 1         | 2        |                                       |            |               |           |                          |                    |

| PRODUCT NUMBER | SIZE  | DIM "A" | DIM "B" | DIM "C" | DIM "S" | SLOT STYLE      |
|----------------|-------|---------|---------|---------|---------|-----------------|
| 79435-X04      | 2x 2  | 9.54    | 2.54    | 9.46    | 5.66    | NO SLOT         |
| 79435-X06      | 2x 3  | 12.08   | 5.08    | 12.00   | 8.20    | RIGHT IF NO KEY |
| 79435-X08      | 2x 4  | 14.62   | 7.62    | 14.54   | 10.74   | RIGHT IF NO KEY |
| 79435-X10      | 2x 5  | 17.16   | 10.16   | 17.08   | 13.28   | RIGHT SLOT      |
| 79435-X14      | 2x 7  | 22.24   | 15.24   | 22.16   | 18.36   | RIGHT SLOT      |
| 79435-X16      | 2x 8  | 24.78   | 17.78   | 24.70   | 20.90   | 2 SLOTS         |
| 79435-X18      | 2x 9  | 27.32   | 20.32   | 27.24   | 23.44   | 2 SLOTS         |
| 79435-X20      | 2x 10 | 29.86   | 22.86   | 29.78   | 25.98   | 2 SLOTS         |
| 79435-X24      | 2x 12 | 34.94   | 27.94   | 34.85   | 31.06   | 2 SLOTS         |
| 79435-X26      | 2x 13 | 37.48   | 30.48   | 37.40   | 33.60   | 2 SLOTS         |
| 79435-X30      | 2x 15 | 42.56   | 35.56   | 42.48   | 38.68   | 2 SLOTS         |
| 79435-X34      | 2x 17 | 47.64   | 40.64   | 47.56   | 43.76   | 2 SLOTS         |
| 79435-X40      | 2x 20 | 55.26   | 48.26   | 55.18   | 51.38   | 2 SLOTS         |
| 79435-X44      | 2x 22 | 60.34   | 53.34   | 60.26   | 56.46   | 2 SLOTS         |
| 79435-X50      | 2x 25 | 67.96   | 60.96   | 67.88   | 64.08   | 2 SLOTS         |
| 79435-X60      | 2x 30 | 80.66   | 73.66   | 80.58   | 76.78   | 2 SLOTS         |
| 79435-X64      | 2x 32 | 85.74   | 78.74   | 85.66   | 81.86   | 2 SLOTS         |




WITH STANDARD STRAIN RELIEF


AFTER TERMINATION SIDE VIEW OF ASSEMBLY (\* LATCHING DIM ON HEADER)




WITH LOW PROFILE STRAIN RELIEF



WITHOUT STRAIN RELIEF  
DUAL ENTRY COVER



WITHOUT STRAIN RELIEF  
BLIND COVER LEFT ASSY



WITHOUT STRAIN RELIEF  
BLIND COVER RIGHT ASSY

|                |                     |                        |               |         |             |            |       |                         |
|----------------|---------------------|------------------------|---------------|---------|-------------|------------|-------|-------------------------|
| 79435-9YY      |                     | ●                      |               |         | ●           |            | ●     | 904 906 908<br>924 930  |
| 79435-8YY      | ●                   |                        |               |         | ●           |            | ●     | 804 806 808<br>824 830  |
| 79435-7YY      | ●                   |                        |               | ●       |             |            | ●     |                         |
| 79435-6YY      | ●                   |                        | ●             |         |             |            | ●     | 604 606 608             |
| 79435-5YY      |                     | ●                      |               | ●       |             |            | ●     | 504 506 508             |
| 79435-4YY      |                     | ●                      | ●             |         |             |            | ●     | 404 406 408             |
| 79435-3YY      | ●                   |                        |               | ●       |             | ●          |       |                         |
| 79435-2YY      | ●                   |                        | ●             |         |             | ●          |       | 204                     |
| 79435-1YY      |                     | ●                      |               | ●       |             | ●          |       |                         |
| 79435-0YY      |                     | ●                      | ●             |         |             | ●          |       | 004                     |
| PRODUCT NUMBER | WITH<br>CENTRAL KEY | WITHOUT<br>CENTRAL KEY | STANDARD      | WITHOUT | LOW PROFILE | DUAL ENTRY | BLIND | DASHES NOT<br>AVAILABLE |
|                |                     |                        | STRAIN RELIEF |         |             | COVER      |       |                         |

|             |          |       |          |                                       |                                                                                                     |                                          |                            |                 |                 |                                                                                                                                |       |
|-------------|----------|-------|----------|---------------------------------------|-----------------------------------------------------------------------------------------------------|------------------------------------------|----------------------------|-----------------|-----------------|--------------------------------------------------------------------------------------------------------------------------------|-------|
| mat'l. code |          |       |          | tolerances unless otherwise specified |                                                                                                     |                                          |                            | CUSTOMER COPY   |                 |  <b>ELECTRONICS</b><br>www.fciconnect.com |       |
| ltr         | ecn no   | dr    | date     | linear                                | projection<br> | title<br><b>EURO QUICKIE</b><br>2 PIECES | product family<br>QKIE FEM | code<br>213     | sheet<br>2 of - | size<br>A2                                                                                                                     | 79435 |
| F           | V20539   | OMA   | 92.03.23 |                                       |                                                                                                     |                                          |                            |                 |                 |                                                                                                                                |       |
| G           | F10566   | DLE   | 01.10.24 | angles                                | mm [inch]                                                                                           | scale<br>N/A                             | size dwg no<br>79435       | sheet<br>2 of - |                 |                                                                                                                                |       |
| H           | F03019   | DLE   | 03.01.23 |                                       |                                                                                                     |                                          |                            |                 |                 |                                                                                                                                |       |
|             |          |       |          | dr                                    | P NIZZI                                                                                             | 94.02.10                                 |                            |                 |                 |                                                                                                                                |       |
|             |          |       |          | engr                                  | JM PHAMVAN                                                                                          | 94.02.10                                 |                            |                 |                 |                                                                                                                                |       |
|             |          |       |          | chr                                   | O MATHEVON                                                                                          | 91.10.31                                 |                            |                 |                 |                                                                                                                                |       |
|             |          |       |          | appd                                  | JM P                                                                                                | 94.02.10                                 |                            |                 |                 |                                                                                                                                |       |
| sheet index | revision | sheet |          |                                       |                                                                                                     |                                          |                            |                 |                 |                                                                                                                                |       |