

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201095002](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Ultra-Lock (M12) Ethernet Receptacle, 4 Poles, FPM M16, Female (Straight), , D-Code, 0.050m (1.97") Length

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Industrial Receptacles
Series [120109](#)
IP Rating IP67
NEMA Rating NEMA 6
Overview [Brad Industrial Ethernet Solutions](#)
Product Name Ultra-Lock (M12)
Type Single Ended (pigtail)
UPC 883906436834

Physical
Coupling Type Internal Thread
Gender Female
Keyway D-coded
Length 0.050m
Material - Component Nickel-plated Brass
Mounting Thread Size M16 x 1.5
Net Weight 22.679/g
Orientation Straight
Panel Mount N/A
Poles 4
Temperature Range - Operating N/A
Wire Size AWG 22
Wire/Cable Type N/A

Electrical
Current - Maximum per Contact 4.0A
Voltage - Maximum 250V

Material Info
Engineering Number ERWAAU7000C050

Reference - Drawing Numbers
Sales Drawing SD-120109-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120109 Series](#)

Mates With

Ultra Lock M12 Cordsets

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION