



## Panel Mounting




- Battery size AA (R6)
- 1, 2 or 3 Cells
- Panel Mount
- Bayonet/Screwdriver release



- Battery size AA (R6)
- 4 Cells
- Flanged Panel Mount
- Drawer function



- Battery size C (R14)
- 1, 2 or 3 Cells
- Panel Mount
- Screw Cap/Hand release



| Specification          | BX0011/1, BX0012/1, BX0013/1                                      | BX0027                                              | BX0001/1, BX0002/1, BX0003/1                                             |
|------------------------|-------------------------------------------------------------------|-----------------------------------------------------|--------------------------------------------------------------------------|
| Battery/Cell Type:     | AA (R6)                                                           | AA (R6)                                             | C (R14)                                                                  |
| No. Cells:             | BX0011/1 - 1 cell<br>BX0012/1 - 2 cells<br>BX0013/1 - 3 cells     | 4 cells                                             | BX0001/1 - 1 cell<br>BX0002/1 - 2 cells<br>BX0003/1 - 3 cells            |
| Terminations:          | 2.8 series tabs/solder tags                                       | 4 solder tags (can be wired in series or in pairs)  | 2.8 series tabs/solder tags                                              |
| Operating Temperature: | -30°C to +50°C                                                    | -30°C to +70°C                                      | -30°C to +70°C                                                           |
| Mouldings:             | Glass Filled Nylon & Polystyrene                                  | Glass Filled Nylon                                  | Nylon & Glass Filled Nylon                                               |
| Contacts:              | Brass, Tin Plated<br>Nickel Silver, clean                         | Phosphor Bronze, Tin Plated<br>Nickel Silver, clean | Nickel Silver, clean<br>Brass, Tin Plated                                |
| Features:              | Bayonet cap with coin slot. Body may be supported by rear bracket | Removable loading/latching drawer                   | Screw on cap. Recommended torque for panel ring 1.13-1.7Nm (10-15lbf.in) |