

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130111-0031

Status:


Active

Overview:

Stringlights

Description:

Safety Yellow® Molded Stringlight, 200W, 12/3 SJTW with 2.43m Lead 5 Sockets Full Ground Ring, Overall Length 15.24m (50.0')



Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

UL

E112216

General

Product Family

Series

NEMA Configuration

NEMA Rating

Outlet

Overview

Product Literature Order No

Product Name

Type

UPC

Woodhead

Portable Lighting

130111

NEMA 5-15

Rain Tight

None

Stringlights

987650-8055

Safety Yellow®

String Lights

78678840870

Yes

Physical

Cord Length - Primary

Cord Length - Secondary

Depth

Duty

Guard Included

Guard Type

Height

Length

Material - Guard

Mounting Style

Net Weight

Packaging Type

Socket Construction

2.43m (8.0')

0.61m (2.0')

N/A

Commercial

No

N/A

N/A

15.24m (50.0')

N/A

Stringer

5.230/kg

Carton

Molded

Electrical

Bulb Type

Cord Type - Primary

Lamp Type

Lamp Wattage - Maximum

Lumens

On/Off Switch

Voltage (Fixture) - Maximum

Incandescent

12/3 SJTW

A21

200W

2000

No

120VAC 60 HZ

Material Info

Old Part Number

5003

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130111Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION